


TECHSPEC® 12.7mm Dia Protected Silver, 4-6λ Mirror



Stock **#36-040** **20+ In Stock**

⊖ 1 ⊕ ₹2,316

ADD TO CART

Volume Pricing	
Qty 1-5	₹2,316 each
Qty 6-25	₹1,732 each
Qty 26-99	₹1,654 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

12.70 ±0.25 **Diameter (mm):**

±0.25 **Dimensional Tolerance (mm):**

11.70 **Clear Aperture CA (mm):**

Edges:
Ground, 0.5mm Maximum Edge Chip

Thickness (mm):
2.00 nominal

Optical Properties

4 - 6λ **Surface Flatness (P-V):**

Float Glass **Substrate:**

60-40 **Surface Quality:**

Coating Specification:
R_{avg} >98% @450 - 800nm
R_{avg} >98.5% @2000 - 10,000nm

Protected Silver (450-10000nm) **Coating:**

Metal **Coating Type:**

450 - 10000 **Wavelength Range (nm):**

Damage Threshold, By Design:
0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)


Product Details

- Wide Variety of Shapes and Sizes Available
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings for high reflectivity from 450-10000nm
- [Contact Us](#) for Custom Sizes

TECHSPEC® First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in enhanced aluminum, protected gold, and protected silver coatings for high reflectivity from 450-10000nm. The coated surface should be oriented to reflect incident light. TECHSPEC First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration.

Note: A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

Technical Information



Coating Curves

Compatible Mounts