

TECHSPEC® 12.7mm Dia. x 1000mm ROC, Uncoated, Concave Laser Mirror



TECHSPEC Uncoated Concave Mirrors

Stock #27-596

NEW

5 In Stock

-

1

+

MRP ₹9,002

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,002 each
Qty 6-25	₹8,543 each
Qty 26+	₹8,268 each
Need More?	Request Quote

Product Downloads

General

Type:

Concave Mirror

Physical & Mechanical Properties

Diameter (mm):

12.70 +0.00/-0.12

Back Surface:

Commercial Polish	
5.98	Center Thickness CT (mm):
90	Clear Aperture (%):
6.00 ±0.2	Edge Thickness ET (mm):
Optical Properties	
Uncoated	Coating:
500.00	Effective Focal Length EFL (mm):
Fused Silica (Corning 7980)	Substrate: □
1,000.00	Radius R ₁ (mm):
20-10	Surface Quality:
λ/10	Irregularity (P-V) @ 632.8nm:
1,000.00	Radius of Curvature (mm):
Regulatory Compliance	
View	Certificate of Conformance:
Vietnam	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

TECHSPEC® Uncoated Concave Laser Mirrors offer high precision 20-10 surface quality ideal for laser beam focusing applications. Featuring fused silica substrates, these concave mirrors are resistant to thermal shock and are available in focal lengths from 25mm to 500mm. TECHSPEC Uncoated Concave Laser Mirrors are ideal for applications in environments with temperature fluctuations. Custom coating options including protected metal coatings and dielectric mirror coatings are available.