

TECHSPEC[®] 12.7mm Dia. x 31.8mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-787-INK 17 TO 22 D= DAYS

-

1

+

₹8,352.00

ADD TO CART

Qty 1-5

₹8,352.00

Qty 6+

₹6,677.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.70 ±0.025

Effective Focal Length EFL (mm):
31.75

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 28.83
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.70
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.75 ±0.20
Center Thickness CT 1 (mm) : 4.00 ±0.10
Center Thickness CT 2 (mm) : 1.75 ±0.10
Radius R₁ (mm) : 21.13
Radius R₂ (mm) : -16.69
Radius R₃ (mm) : -61.73
Edge Thickness ET (mm) : 4.45
Substrate : ☐ N-SSK8 / SF56
Surface Quality : 40-20
f/# : 2.5
Numerical Aperture NA : 0.20
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View