

[See all 16 Products in Family](#)

TECHSPEC® 12.7mm Dia. x 12.7mm EFL, 532nm Dielectric Off-Axis Parabolic Mirror



TECHSPEC® Laser Line Coated Off-Axis Parabolic (OAP) Mirrors

Stock **#15-339** **2 In Stock**

[Other Coating Options](#)

1 MRP ₹34,404

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹34,404 each
Qty 6-10	₹30,974 each
Qty 11-25	₹29,258 each
Need More?	Request Quote

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

12.7 **Y Offset (mm):**

12.70 +0.0/-0.1	Diameter (mm):
90	Clear Aperture (%):
<50 RMS	Surface Roughness (□):
Optical Properties	
Dielectric	Coating Type:
Dielectric Mirror (532nm)	Coating:
90	Off-Set Angle (°):
532	Wavelength Range (nm):
12.70	Effective Focal Length EFL (mm):
Aluminum 6061-T6	Substrate: □
R _{avg} >99.5% @ 532nm	Coating Specification:
±1	Focal Length Tolerance (%):
6.35	Parent Focal Length PFL (mm):
λ/8	Surface Figure, RMS:
60-40	Surface Quality:
12.70	Radius of Curvature (mm):
λ/4	Reflected Wavefront, RMS:

Threading & Mounting	
#34-425	Compatible Mounting Plates:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Dielectric Laser Line Coatings for 532 and 1064nm
- Ideal for Collimating or Focusing Nd:YAG Laser Light
- >99.5% Reflectivity at Nd:YAG Design Wavelengths
- [Metallic Coated Off-Axis Parabolic Mirrors](#) Also Available

TECHSPEC® Laser Line Coated Off-Axis Parabolic (OAP) Mirrors feature diamond turned aluminum substrates coated with dielectric coatings for high reflection at 532 or 1064nm laser lines. These high reflectivity dielectric coatings are designed for laser applications that require higher performance than metallic coated optics can provide. Standard imperial sizes are available with multiple focal length options, and mounting plates with holes perpendicular to the optical axis are also available for benchtop integration. TECHSPEC® Laser Line Coated Off-Axis Parabolic (OAP) Mirrors are ideal for use with the fundamental or second harmonic of Nd:YAG lasers to collimate or focus laser light.

Technical Information

