

TECHSPEC® 12.7mm Dia. x 38.1mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-775-INK** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹7,917.00**

ADD TO CART

Qty 1-5
₹7,917.00
Qty 6+
₹6,329.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.70 ±0.025

Effective Focal Length EFL (mm):
38.10

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 35.57
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.70
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.20
Center Thickness CT 1 (mm): 3.50 ±0.10
Center Thickness CT 2 (mm): 1.50 ±0.10
Radius R₁ (mm): 25.43
Radius R₂ (mm): -20.03
Radius R₃ (mm): -74.39
Edge Thickness ET (mm): 3.92
Substrate: ☐ N-SSK0 / SF56
Surface Quality: 40-20
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View