

[See all 5 Products in Family](#)

12mm, 0.59mm Focal Length, Fast Axis Collimator



Fast Axis Collimators

Stock **#87-351** **8 In Stock**

MRP ₹21,187

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹21,187 each
Qty 11-49	₹19,069 each
Need More?	Request Quote

Product Downloads

General

Beam Shaping Lens **Type:**

Physical & Mechanical Properties

11.0 x 0.9 **Clear Aperture CA (mm):**

1.00 **Height (mm):**

±0.05 **Height Tolerance (mm):**

12.00 **Length (mm):**

±0.05 **Length Tolerance (mm):**

0.80 **Width (mm):**

±0.01 **Width Tolerance (mm):**

Optical Properties

0.59 **Effective Focal Length EFL (mm):**

S-TIH53 **Substrate:**

0.63 **f#:**

0.80 **Numerical Aperture NA:**

BBAR (790-990nm) **Coating:**

790 - 990 **Wavelength Range (nm):**

0.15 **Back Focal Length BFL (mm):**

$R_{avg} < 1.0\%$ @ 790 - 990nm **Coating Specification:**

$\lambda/4$ **Surface Accuracy:**

>99 **Transmission (%):**

Electrical

within ± 1.1 : >85 **Power Distribution (%):**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 197:**

View **Certificate of Conformance:**

Germany **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Aspheric Cylindrical Lens Designs for Fast Axis Collimation
- Standard AR Coating for 790 – 990nm
- Ideal for Laser Diode Collimation
- [Slow Axis Collimators](#) Also Available

Fast Axis Collimators are compact, high performance aspheric cylindrical lenses designed for beam shaping or laser diode collimation applications. The aspheric cylindrical designs and high numerical apertures allow for uniform collimation of the entire output of a laser diode while maintaining high beam quality. Fast Axis Collimators feature greater than 99% transmission across the designated spectral range, and are available in a variety of focal lengths.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)