

12.7mm Dia. x 8mm FL, MgF₂ Coated, Aspheric Condenser Lens



Stock **#21-195**

10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹3,828.00

ADD TO CART

Qty 1-10
₹3,828.00
Qty 11+
₹3,480.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 12.70 +0.0/-0.2
Effective Focal Length EFL (mm): 8.00
Numerical Aperture NA: 0.79
Back Focal Length BFL (mm):

3.7
Substrate: H-K51
Focal Length Tolerance (%): ±5
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 11.43
Edge Thickness ET (mm): 1.86
Center Thickness CT (mm): 7.50 ±0.30
f#: 0.63
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 12.7
Radius R₂ (mm): 15.65
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant