

TECHSPEC[®] 12.7mm Diameter x 100mm FL, 950-1150nm Coated, Ultrafast Thin PCX Lens



Stock **#11-635** 7 In Stock

☐ [Other Coating Options](#)

-

1

+

₹7,668

ADD TO CART

Volume Pricing	
Qty 1-5	₹7,668 each
Qty 6+	₹6,773 each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

12.70 +0.00/-0.10

Centering (arcmin):

<3

Center Thickness CT (mm):

1.50 ±0.10	
	Edge Thickness ET (mm):
1.06	
	Clear Aperture CA (mm):
11.43	
	Bevel:
Protective as needed	

Optical Properties

	Effective Focal Length EFL (mm):
100.12 @ 587.6nm	
	Back Focal Length BFL (mm):
99.09	
	Coating:
BBAR (950-1150nm)	
	Coating Specification:
R _{abs} <0.15% @ 950 - 1150nm	
	Substrate: ☐
Fused Silica (Corning 7980)	
	Surface Quality:
20-10	
	Power (P-V) @ 632.8nm:
1.5λ	
	Irregularity (P-V) @ 632.8nm:
λ/8	
	Focal Length Tolerance (%):
±1	
	Radius R ₁ (mm):
45.90	
	f/#:
7.88	
	Numerical Aperture NA:
0.064	
	Design Wavelength DWL (nm):
1030	
	Wavelength Range (nm):
950 - 1150	
	Angle of Incidence (°):
0	
	Damage Threshold, By Design: ☐
10 J/cm ² @ 532nm, 20ns, 20Hz	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Reach 219:
Compliant	
	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	


Product Details

- Ultra-Thin Center Thickness to Limit GDD
- Low Loss Broadband IBS Anti-Reflection Coating
- Ideal for Ultrafast and Laser Optics Applications
- UV or IR Grade Fused Silica Substrates

TECHSPEC® Ultrafast Thin Plano-Convex Lenses are designed with an ultra-thin center thickness to provide a low group delay dispersion (GDD) for ultrafast laser pulses. TECHSPEC Ultrafast Thin Plano-Convex Lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics, including Ti:sapphire, Yb:YAG, and Nd:YAG, Holmium, and Thulium lasers. These thin PCX lenses are available in standard sizes with effective focal lengths from 50mm to 2000mm.

IR grade fused silica differs from UV grade fused silica by its reduced amount of OH⁻ ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts