


[See all 3 Products in Family](#)

12.7mm, MgF₂ Coated, Penta Prism Beamsplitter



Stock #66-632 **4 In Stock**

MRP ₹25,728

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹25,728 each
Qty 6-25	₹20,582 each
Qty 26-49	₹19,069 each
Need More?	Request Quote

Product Downloads

General

Standard Beamsplitter **Type:**

Physical & Mechanical Properties

>90 **Clear Aperture (%):**

Prism **Construction:**

± 0.10	Dimensional Tolerance (mm):
Optical Properties	
90, 180	Beam Deviation (°):
± 10	Beam Deviation Tolerance (arcsec):
MgF ₂ on Entrance and Exit Faces	Coating:
$ T_s - T_p \leq 15\%$	Polarization:
50/50	Reflection/Transmission Ratio (R/T):
± 5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: <input type="checkbox"/>
$\lambda/4$	Surface Flatness (P-V):
40-20	Surface Quality:
450 - 650	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:


Product Details

- 50% Reflection / 50% Transmission
- Beam Deviation Insensitive to Alignment
- Designed for Visible Wavelengths

Penta Prism Beamsplitters are constructed by cementing a precision [penta prism](#) and a [wedge prism](#) together, and applying an appropriate interference coating to one of the traditionally reflective surfaces. Since slight movements of a penta prism do not affect the true right angle at which light rays are reflected, the deviation between the transmitted and reflected light rays is highly controllable and will not vary by more than 10arcsec.

Note: Outgoing beams are partially polarized.

Technical Information



Stock No.	A	B	C	D	E
#66-632	12.70mm	12.70mm	5.26mm	13.75mm	12.70mm
#66-633	20.00mm	20.00mm	8.28mm	21.65mm	20.00mm
#66-634	25.40mm	25.40mm	10.52mm	27.49mm	25.40mm
