

[See all 31 Products in Family](#)

**TECHSPEC® 12mm Dia. x 30mm FL 1550nm V-Coat, UV PCX Lens**



Stock #34-158 [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹15,537

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹15,537 each
Qty 6-25	₹12,410 each
Qty 26-49	₹11,703 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

**Diameter (mm):**

12.00 +0.0/-0.025

**Centering (arcmin):**

≤1

**Center Thickness CT (mm):**

3.55 ±0.05

**Edge Thickness ET (mm):**

2.17

**Clear Aperture CA (mm):**

11.00

**Bevel:**

Protective as needed

**Edges:**

Fine Ground, Protective Bevel as Needed

## Optical Properties

**Effective Focal Length EFL (mm):**

30.00 @ 587.6nm

**Back Focal Length BFL (mm):**

27.56

**Coating:**

Laser V-Coat (1550nm)

**Coating Specification:**

R<sub>abs</sub> <0.25% @ 1550nm

**Substrate:**

[Fused Silica](#) (Corning 7980)

**Surface Quality:**

40-20

**Power (P-V) @ 632.8nm:**

1.5λ

**Irregularity (P-V) @ 632.8nm:**

λ/4

**Focal Length Tolerance (%):**

±1

**Radius R<sub>1</sub> (mm):**

13.75

**f#:**

2.50

**Numerical Aperture NA:**

0.20

**Design Wavelength DWL (nm):**

587.6

**Damage Threshold, By Design:**

5 J/cm<sup>2</sup> @ 1550nm, 10ns

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 235:**

[Compliant](#)

**Country of Origin:**

Japan

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at 1550nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [633nm](#), and [1064nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.

## Compatible Mounts

---