

[See all 245 Products in Family](#)

TECHSPEC<sup>®</sup> 12mm Dia. x 35mm FL, NIR II Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#22-182 4 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹10,510

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,510 each                  |
| Qty 6-25       | ₹8,408 each                   |
| Qty 26-49      | ₹7,863 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                           |                      |
|---------------------------|----------------------|
| 12.00 +0.0/-0.025         |                      |
| Centering (arcmin):       | <1                   |
| Bevel:                    | Protective as needed |
| Center Thickness CT (mm): | 3.29 ±0.05           |
| Edge Thickness ET (mm):   | 2.14                 |
| Clear Aperture CA (mm):   | 11.00                |

|                                                       |                                                                                                                        |
|-------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|
| Optical Properties                                    |                                                                                                                        |
| Back Focal Length BFL (mm):                           | 33.85                                                                                                                  |
| Effective Focal Length EFL (mm):                      | 35.00                                                                                                                  |
| Coating:                                              | NIR II (750-1550nm)                                                                                                    |
| Coating Specification:                                | R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |
| Substrate: <input type="checkbox"/>                   | <b>Fused Silica</b> (Corning 7980)                                                                                     |
| Surface Quality:                                      | 40-20                                                                                                                  |
| Power (P-V) @ 632.8nm:                                | 1.5λ                                                                                                                   |
| Irregularity (P-V) @ 632.8nm:                         | λ/4                                                                                                                    |
| Radius R <sub>1</sub> =R <sub>2</sub> (mm):           | 31.57                                                                                                                  |
| f/#:                                                  | 2.92                                                                                                                   |
| Focal Length Specification Wavelength (nm):           | 587.6                                                                                                                  |
| Focal Length Tolerance (%):                           | ±1                                                                                                                     |
| Numerical Aperture NA:                                | 0.17                                                                                                                   |
| Wavelength Range (nm):                                | 750 - 1550                                                                                                             |
| Damage Threshold, Reference: <input type="checkbox"/> | 8 J/cm <sup>2</sup> @ 1064nm, 10ns                                                                                     |

|                             |                                     |
|-----------------------------|-------------------------------------|
| Regulatory Compliance       |                                     |
| RoHS 2015:                  | <b>Compliant</b>                    |
| Certificate of Conformance: | <b>View</b>                         |
| Reach 235:                  | <b>Compliant</b>                    |
| Country of Origin:          | Japan                               |
| Imported By:                | Edmund Optics India Private Limited |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma



- Precision Fused Silica Substrate

TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.






Technical Information



UV FS Transmission Curve



| FUSED SILICA                                                                                                  |  |                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p>Uncoated Fused Silica<br/>Typical Transmission</p> <p>T (%)</p> <p>Wavelength (nm)</p>                     |  | <p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                              |
| <p>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</p> <p>T (%)</p> <p>Wavelength (nm)</p> |  | <p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

|                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <p data-bbox="583 290 1075 394"><b>Fused Silica with UV-AR Coating</b><br/><b>Typical Transmission</b></p>        | <p data-bbox="1329 448 1854 498">Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p data-bbox="1329 513 1854 563">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 575 1707 649"><math>R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}</math><math>R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}</math><math>R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}</math></div> <p data-bbox="1329 661 1854 709">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 724 1707 744"><a href="#">Click Here to Download Data</a></p>           |
| <p data-bbox="583 970 1075 1074"><b>Fused Silica with UV-VIS Coating</b><br/><b>Typical Transmission</b></p>    | <p data-bbox="1329 1127 1854 1178">Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1193 1854 1243">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 1255 1707 1302"><math>R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}</math><math>R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}</math></div> <p data-bbox="1329 1338 1854 1386">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 1400 1707 1421"><a href="#">Click Here to Download Data</a></p>                                                              |
| <p data-bbox="583 1650 1075 1754"><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 1831 1854 1881">Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1896 1854 1944">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 1955 1707 1979"><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div> <p data-bbox="1329 1994 1854 2041">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 2056 1707 2077"><a href="#">Click Here to Download Data</a></p>                                                                                                                          |
| <p data-bbox="583 2329 1075 2433"><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 2469 1854 2519">Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p data-bbox="1329 2534 1854 2582">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 2594 1707 2668"><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div> <p data-bbox="1329 2703 1854 2751">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 2766 1707 2786"><a href="#">Click Here to Download Data</a></p> |



