

# 12mm Dia x -25.8mm FL Enhanced Aluminum Coated, Convex Mirror



Stock **#64-059** 1 In Stock

-

1

+

₹3,231

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹3,231 each                   |
| Qty 6-25       | ₹2,919 each                   |
| Qty 26-49      | ₹2,744 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

12.00 +0.00/-0.10

Diameter (mm):

8.06

Center Thickness CT (mm):

|                                     |                                                       |
|-------------------------------------|-------------------------------------------------------|
| 90                                  | Clear Aperture (%):                                   |
| 1.73                                | Edge Thickness ET (mm):                               |
| 51.68                               | Radius R (mm):                                        |
| Optical Properties                  |                                                       |
| -25.80                              | Focal Length FL (mm):                                 |
| Enhanced Aluminum (450-650nm)       | Coating:                                              |
| R <sub>avg</sub> >95% @450 - 650nm  | Coating Specification:                                |
| Metal                               | Coating Type:                                         |
| ±2                                  | Focal Length Tolerance (%):                           |
| N-BK7                               | Substrate: <input type="checkbox"/>                   |
| 60-40                               | Surface Quality:                                      |
| 450 - 650                           | Wavelength Range (nm):                                |
| 0.2 J/cm <sup>2</sup> @ 532nm, 10ns | Damage Threshold, Reference: <input type="checkbox"/> |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 247:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Variety of Diameters and Focal Lengths Available
- Enhanced Aluminum and Protected Gold Coatings
- Ideal for Imaging Systems

Convex Spherical Mirrors feature a polished plano second surface and convex first surface. Used primarily for increasing an imaging system's field of view, convex mirrors create a virtual, upright image. Shorter focal lengths provide wider fields of view, while longer focal lengths provide less distortion. Convex Spherical Mirrors with Enhanced Aluminum coatings are ideal for applications in the visible spectrum, while Protected Gold provides excellent reflection throughout the NIR, MMIR, and LMIR spectra. The mirrors are offered in 12, 25, and 50mm diameters, in a variety of wavelength ranges.

## Coating Curves