

12mm Dia x -6.1mm FL Enhanced Aluminum Coated, Convex Mirror



Stock **#64-055** 9 In Stock

-

1

+

₹3,231

ADD TO CART

Volume Pricing	
Qty 1-5	₹3,231 each
Qty 6-25	₹2,919 each
Qty 26-49	₹2,744 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

12.00 +0.00/-0.10

Diameter (mm):

3.00

Center Thickness CT (mm):

90	Clear Aperture (%):
1.41	Edge Thickness ET (mm):
12.11	Radius R (mm):
Optical Properties	
-6.10	Focal Length FL (mm):
Enhanced Aluminum (450-650nm)	Coating:
R _{avg} >95% @450 - 650nm	Coating Specification:
Metal	Coating Type:
±2	Focal Length Tolerance (%):
N-SF5	Substrate: □
60-40	Surface Quality:
450 - 650	Wavelength Range (nm):
0.2 J/cm ² @ 532nm, 10ns	Damage Threshold, Reference: □
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Variety of Diameters and Focal Lengths Available
- Enhanced Aluminum and Protected Gold Coatings
- Ideal for Imaging Systems

Convex Spherical Mirrors feature a polished plano second surface and convex first surface. Used primarily for increasing an imaging system's field of view, convex mirrors create a virtual, upright image. Shorter focal lengths provide wider fields of view, while longer focal lengths provide less distortion. Convex Spherical Mirrors with Enhanced Aluminum coatings are ideal for applications in the visible spectrum, while Protected Gold provides excellent reflection throughout the NIR, MMIR, and LMIR spectra. The mirrors are offered in 12, 25, and 50mm diameters, in a variety of wavelength ranges.

Coating Curves