

[See all 31 Products in Family](#)

TECHSPEC[®] 12mm Dia. x 50mm FL 405nm V-Coat, UV PCX Lens



Stock **#34-068** 4 In Stock

☐ [Other Coating Options](#)

-

1

+

₹10,354

ADD TO CART

Volume Pricing	
Qty 1-5	₹10,354 each
Qty 6-25	₹8,252 each
Qty 26-49	₹7,785 each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

12.00 +0.0/-0.025

≤1	Centering (arcmin):
2.90 ±0.05	Center Thickness CT (mm):
2.1	Edge Thickness ET (mm):
11	Clear Aperture CA (mm):
Protective as needed	Bevel:
Fine Ground, Protective Bevel as Needed	Edges:

Optical Properties	
50.00 @ 587.6nm	Effective Focal Length EFL (mm):
48.01	Back Focal Length BFL (mm):
Laser V-Coat (405nm)	Coating:
R _{abs} <0.25% @ 405nm	Coating Specification:
Fused Silica (Corning 7980)	Substrate: □
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
22.92	Radius R ₁ (mm):
4.17	f##:
0.12	Numerical Aperture NA:
405	Design Wavelength DWL (nm):
3 J/cm² @ 405nm, 10ns	Damage Threshold, By Design: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- <0.25% Reflection at 405nm for 405nm Diodes
 - 5 - 50mm Diameters Available
 - 10 - 250mm EFL Designs Available
 - [532nm](#), [633nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered
- TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.></0.25%>

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

• Scalable production—from prototype to volume
Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
