

TECHSPEC<sup>®</sup> 12mm, f/4 UCi Series Fixed Focal Length Lens



12mm UCi Series Fixed Focal Length Lens



Stock **#33-878** **5 In Stock**

-

1

+

₹16,356

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹16,356 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                |
|----------------------------------|----------------|
| UCi Series                       | Series:        |
| Fixed Focal Length Lens          | Type:          |
| No                               | IR Cut Filter: |
| Physical & Mechanical Properties |                |

|       |                               |
|-------|-------------------------------|
| Fixed | Iris Option:                  |
|       |                               |
| 38.00 | Length (mm):                  |
|       |                               |
| 22    | Maximum Diameter (mm):        |
|       |                               |
| 22    | Outer Diameter (mm):          |
|       |                               |
| 18    | Weight (g):                   |
|       |                               |
| 0     | Maximum Rear Protrusion (mm): |
|       |                               |

| Optical Properties                                                               |                                               |
|----------------------------------------------------------------------------------|-----------------------------------------------|
| 69.2mm - 34.0°                                                                   | Horizontal Field of View @ Max Sensor Format: |
|                                                                                  |                                               |
| Horizontal: 69.2mm - 34°<br>Vertical: 51.4mm - 25.6°<br>Diagonal: 87.6mm - 42.2° | Field of View at Max Sensor Format:           |
|                                                                                  |                                               |
|                                                                                  |                                               |
|                                                                                  |                                               |
| 69.2mm - 34.0°                                                                   | Horizontal Field of View, 1/1.8" Sensor:      |
|                                                                                  |                                               |
| 61.2mm - 30.3°                                                                   | Horizontal Field of View, 1/2" Sensor:        |
|                                                                                  |                                               |
| 55.3mm - 27.5°                                                                   | Horizontal Field of View, 1/2.5" Sensor:      |
|                                                                                  |                                               |
| 45.5mm - 22.8°                                                                   | Horizontal Field of View, 1/3" Sensor:        |
|                                                                                  |                                               |
| 34.0mm - 17.1°                                                                   | Horizontal Field of View, 1/4" Sensor:        |
|                                                                                  |                                               |
| 9.00                                                                             | Maximum Image Circle (mm):                    |
|                                                                                  |                                               |
| 0.0128                                                                           | Numerical Aperture NA, Object Side:           |
|                                                                                  |                                               |
| 7 (6)                                                                            | Number of Elements (Groups):                  |
|                                                                                  |                                               |
| 12.00                                                                            | Focal Length FL (mm):                         |
|                                                                                  |                                               |
| 100 - ∞                                                                          | Working Distance (mm):                        |
|                                                                                  |                                               |
| f/4.0                                                                            | Aperture (f/#):                               |
|                                                                                  |                                               |
| λ/4 MgF <sub>2</sub>                                                             | Coating:                                      |
|                                                                                  |                                               |
| λ/4 MgF <sub>2</sub>                                                             | Coating Specification:                        |
|                                                                                  |                                               |
| 15.92                                                                            | Entrance Pupil Position (mm):                 |
|                                                                                  |                                               |
| 23.03                                                                            | Object Space Principal Plane (mm):            |
|                                                                                  |                                               |
| -1.82                                                                            | Image Space Principal Plane (mm):             |
|                                                                                  |                                               |
| -3.03                                                                            | Maximum Distortion (%):                       |
|                                                                                  |                                               |
| -19.24                                                                           | Exit Pupil Position (mm):                     |
|                                                                                  |                                               |
| VIS                                                                              | Lens Wavelength Range:                        |
|                                                                                  |                                               |

| Sensor |                          |
|--------|--------------------------|
| 1/2.5" | Optimized Sensor Format: |
|        |                          |
| 1/1.8" | Maximum Sensor Format:   |
|        |                          |
| 1.85   | Pixel Size (μm):         |
|        |                          |

| Threading & Mounting |                |
|----------------------|----------------|
| M22 x0.75 (Male)     | Filter Thread: |
|                      |                |
| S-Mount (M12 x0.5)   | Mount:         |
|                      |                |

| Environmental & Durability Factors |                           |
|------------------------------------|---------------------------|
|                                    | Storage Temperature (°C): |
|                                    |                           |

-20 to +60

Type of Ruggedization:  
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

CompliantRoHS 2015:

CompliantReach 224:

ViewCertificate of Conformance:

ChinaCountry of Origin:

Edmund Optics India Private LimitedImported By:

Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels ≤2.2µm and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

**Note:** For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


**UCr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


Technical Information




#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Distortion Plot



#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 100mm Working Distance, f4



#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Depth of Field Plot, 100mm Working Distance, f4



#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 400mm Working Distance, f4



#33-878, 12mm, f/4 UCi Series Fixed Focal Length Lens, Depth of Field Plot, 400mm Working Distance, f4

## Compatible Cameras