

[See all 245 Products in Family](#)

TECHSPEC<sup>®</sup> 12mm Dia. x 75mm FL, NIR II Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#22-187 4 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹10,510

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,510 each                  |
| Qty 6-25       | ₹8,408 each                   |
| Qty 26-49      | ₹7,863 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                           |                      |
|---------------------------|----------------------|
| 12.00 +0.0/-0.025         |                      |
| Centering (arcmin):       | <1                   |
| Bevel:                    | Protective as needed |
| Center Thickness CT (mm): | 2.59 ±0.05           |
| Edge Thickness ET (mm):   | 2.06                 |
| Clear Aperture CA (mm):   | 11.00                |

|                                                       |                                                                                                                        |
|-------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|
| Optical Properties                                    |                                                                                                                        |
| Back Focal Length BFL (mm):                           | 74.11                                                                                                                  |
| Effective Focal Length EFL (mm):                      | 75.00                                                                                                                  |
| Coating:                                              | NIR II (750-1550nm)                                                                                                    |
| Coating Specification:                                | R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |
| Substrate: <input type="checkbox"/>                   | <b>Fused Silica</b> (Corning 7980)                                                                                     |
| Surface Quality:                                      | 40-20                                                                                                                  |
| Power (P-V) @ 632.8nm:                                | 1.5λ                                                                                                                   |
| Irregularity (P-V) @ 632.8nm:                         | λ/4                                                                                                                    |
| Radius R <sub>1</sub> =R <sub>2</sub> (mm):           | 68.36                                                                                                                  |
| f/#:                                                  | 6.25                                                                                                                   |
| Focal Length Specification Wavelength (nm):           | 587.6                                                                                                                  |
| Focal Length Tolerance (%):                           | ±1                                                                                                                     |
| Numerical Aperture NA:                                | 0.08                                                                                                                   |
| Wavelength Range (nm):                                | 750 - 1550                                                                                                             |
| Damage Threshold, Reference: <input type="checkbox"/> | 8 J/cm <sup>2</sup> @ 1064nm, 10ns                                                                                     |

|                             |                                     |
|-----------------------------|-------------------------------------|
| Regulatory Compliance       |                                     |
| RoHS 2015:                  | <b>Compliant</b>                    |
| Certificate of Conformance: | <b>View</b>                         |
| Reach 235:                  | <b>Compliant</b>                    |
| Country of Origin:          | Japan                               |
| Imported By:                | Edmund Optics India Private Limited |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma



- Precision Fused Silica Substrate

TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.






Technical Information







UV FS Transmission Curve



| FUSED SILICA                                                                                                  |  |                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p>Uncoated Fused Silica<br/>Typical Transmission</p> <p>T (%)</p> <p>Wavelength (nm)</p>                     |  | <p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                              |
| <p>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</p> <p>T (%)</p> <p>Wavelength (nm)</p> |  | <p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm (N-BK7)}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

|                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <p data-bbox="583 290 1075 394"><b>Fused Silica with UV-AR Coating</b><br/><b>Typical Transmission</b></p>        | <p data-bbox="1329 448 1854 498">Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p data-bbox="1329 513 1854 563">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 575 1707 649"><math>R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}</math><math>R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}</math><math>R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}</math></div> <p data-bbox="1329 661 1854 712">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 724 1707 744"><a href="#">Click Here to Download Data</a></p>           |
| <p data-bbox="583 970 1075 1074"><b>Fused Silica with UV-VIS Coating</b><br/><b>Typical Transmission</b></p>    | <p data-bbox="1329 1127 1854 1178">Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1193 1854 1243">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 1255 1707 1302"><math>R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}</math><math>R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}</math></div> <p data-bbox="1329 1338 1854 1389">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 1400 1707 1421"><a href="#">Click Here to Download Data</a></p>                                                              |
| <p data-bbox="583 1650 1075 1754"><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 1831 1854 1881">Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1896 1854 1947">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 1958 1707 1979"><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div> <p data-bbox="1329 1991 1854 2041">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 2053 1707 2074"><a href="#">Click Here to Download Data</a></p>                                                                                                                          |
| <p data-bbox="583 2329 1075 2433"><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 2469 1854 2519">Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p data-bbox="1329 2534 1854 2585">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 2597 1707 2668"><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div> <p data-bbox="1329 2703 1854 2754">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 2766 1707 2786"><a href="#">Click Here to Download Data</a></p> |

|                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p style="text-align: center;"><b>Wavelength (nm)</b></p> <p style="text-align: center;"><b>Fused Silica with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>  <p style="text-align: center;"><b>Wavelength (nm)</b></p> | <p>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p style="text-align: center;"><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p style="text-align: center;"><a href="#">Click Here to Download Data</a></p>                                                                                                                        |
| <p style="text-align: center;"><b>Fused Silica with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  <p style="text-align: center;"><b>Wavelength (nm)</b></p>                                                        | <p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p style="text-align: center;"><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math><br/><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p style="text-align: center;"><a href="#">Click Here to Download Data</a></p>           |
| <p style="text-align: center;"><b>Fused Silica with NIR I Coating</b><br/><b>Typical Transmission</b></p>  <p style="text-align: center;"><b>Wavelength (nm)</b></p>                                                          | <p>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p style="text-align: center;"><math>R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p style="text-align: center;"><a href="#">Click Here to Download Data</a></p>                                                                                                                     |
| <p style="text-align: center;"><b>Fused Silica with NIR II Coating</b><br/><b>Typical Transmission</b></p>  <p style="text-align: center;"><b>Wavelength (nm)</b></p>                                                         | <p>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p style="text-align: center;"><math>R_{abs} \leq 1.5\% @ 750 - 800\text{nm}</math><br/><math>R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}</math><br/><math>R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p style="text-align: center;"><a href="#">Click Here to Download Data</a></p> |

