

[See all 10 Products in Family](#)

TECHSPEC® 12mm LT Series Fixed Focal Length Lens



12mm FL Front, #14-361



Stock **#14-361** CLEARANCE **2 In Stock**

MRP ₹1,52,397

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,52,397 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

LT Series **Product Family:**

Diameter includes liquid lens **Note:**

Type:

Fixed Focal Length Lens

Integrated Liquid Lens Model:
Optutune EL-16-40-TC

Imaging Lens Type:
Integrated Liquid Lens to Adjust Focus Electronically

Special Type of Lens:
Liquid Lens Focusable

Physical & Mechanical Properties

Iris Option:
Fixed

Length (mm):
74.30

Maximum Diameter (mm):
82

Outer Diameter (mm):
82

Weight (g):
245.5

Maximum Rear Protrusion (mm):
0

Optical Properties

Horizontal Field of View @ Max Sensor Format:
432.6mm - 60.0°

Field of View at Max Sensor Format:
Horizontal: 434.3mm - 59.2°
Vertical: 321mm - 45.7°
Diagonal: 552.2mm - 71.5°

Horizontal Field of View, 1.1" Sensor:
432.6mm - 60.0°

Horizontal Field of View, 1" Sensor:
387.6mm - 54.7°

Horizontal Field of View, 2/3" Sensor:
262.3mm - 38.8°

Horizontal Field of View, 1/1.8" Sensor:
213.6mm - 32.0°

Horizontal Field of View, 1/2" Sensor:
189.4mm - 28.5°

Horizontal Field of View, 1/2.5" Sensor:
171.4mm - 25.9°

Horizontal Field of View, 1/3" Sensor:
141.5mm - 21.5°

Horizontal Field of View, 1/4" Sensor:
105.9mm - 16.2°

Maximum Image Circle (mm):
17.60

Numerical Aperture NA, Object Side:
0.006

Number of Elements (Groups):
10 (9)

Focal Length FL (mm):
12.00

Working Distance (mm):
350 - ∞

Aperture (f/#):
f/2.8

Coating:
λ/4 MgF₂

Coating Specification:
λ/4 MgF₂

Entrance Pupil Position (mm):
31.2

Object Space Principal Plane (mm):
39.92

Image Space Principal Plane (mm):
2.45

Maximum Distortion (%):
-4.23

Exit Pupil Position (mm):
-26.58

Lens Wavelength Range:
VIS

Sensor

1.1" **Maximum Sensor Format:**

2.74 **Pixel Size (µm):**

Threading & Mounting

M62 x0.75 (Male) **Filter Thread:**

[#34-236 \(Required\)](#) **Filter Thread Adapter:**

M48 x0.5 (Male) **Front Thread:**

C-Mount **Mount:**

Environmental & Durability Factors

-20 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 1.1" Sensor, C-Mount Lens, up to 12 MegaPixels, 3.45µm Pixel Size Sensor
- Integrated Liquid Lens Allows for Dynamic Autofocus
- Liquid Tunable (LT) Lens Maximizes the Liquid Lens Capabilities for Resolution, Range and Focus Speed
- 12 to 25mm Focal Length

TECHSPEC® LT Series Fixed Focal Length Lenses feature a high-resolution f/2.8 optical design with an integrated Optotune liquid lens for fast electronic focus. The increased light throughput f/2.8 aperture is ideal for high-speed machine vision applications. When combined with an appropriate camera and software, the focus tunable liquid lens provides the active focus control needed to achieve an autofocus solution. These C-Mount lenses are optimized for 1.1" sensors and have front filter threading to integrate imaging filters to meet application requirements. TECHSPEC® LT Series Fixed Focal Length Lenses are ideal for machine vision and factory automation applications where focusing at multiple distances is required, such as quality inspection systems, rapid automation, and package sorting. The TECHSPEC® LT Series Fixed Focal Length Lenses won the [Gold-Level 2021 Vision Systems Design Innovators Award](#) and [third place 2021 reader's choice inspect Award](#).


inspect

award 2021


winner

Note: Hirose cables (2 length options) and Lens Driver are required for operation and sold separately.


Technical Information




#14-361, 12mm LT Series Fixed Focal Length Lens, Distortion Plot




#14-361, 12mm LT Series Fixed Focal Length Lens, Relative Illumination Plot




#14-361, 12mm LT Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#14-361, 12mm LT Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f2.8




#14-361, 12mm LT Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f2.8



#14-361, 12mm LT Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 1000mm Working Distance, f2.8



#14-361, 12mm LT Series Fixed Focal Length Lens, Depth of Field Plot, 1000mm Working Distance, f2.8



Compatible Cameras