

[See all 30 Products in Family](#)

## 7mm Max. Aperture, Mounted Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock #23-262 **1 In Stock**

⊖ 1 ⊕ MRP ₹13,621

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-4	₹13,621 each
Qty 5-9	₹12,007 each
Qty 10-25	₹11,058 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Mounted **Type:**

### Physical & Mechanical Properties

7.0 **Maximum Aperture (mm):**

**Outer Diameter (mm):**

26.5

**Construction:**  
Anodized Aluminum Alloy, Burnished Spring Steel Leaves

**Inner Diameter (mm):**  
12.0

**Lever Diameter (mm):**  
1.50

**Lever Length (mm):**  
6.00

**Number of Leaves:**  
8.00

**Thickness (mm):**  
4.00

## Optical Properties

**Minimum Aperture (mm):**  
0.5, Typical

## Threading & Mounting

**Mounting Threads:**  
8-32

**Set Screw Thread:**  
4-40

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 235:**  
[Compliant](#)

**Country of Origin:**  
Germany

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Corrosion and High Temperature Resistance Housing
- Anti-Reflective (AR) Spring Steel or Burnished Spring Steel Leaf Options Available
- Mounted Version Features both an English and Metric Tapped Hole for Easy Post Mounting

High Performance Standard Series Iris Diaphragms utilize high-quality materials combined with the highest fabrication standards to guarantee optimum performance and reliability even under extreme environmental conditions. Different leaf and aperture diameter options allow these irises to be successfully integrated into a variety of applications, including imaging and high-temperature environments. Known pin/tab angular deviation allows upfront, accurate assessment of movement requirements. Mounted versions of these diaphragms feature both metric and English tapped holes for easy post mounting. These diaphragms are offered with maximum apertures of 5 – 75mm and that have outer diameters ranging from 10 to 100mm. High Performance Standard Series Iris Diaphragms are constructed of a corrosion-resistant, matte finish, black anodized aluminum alloy.

For specific OEM application assistance, please contact our [Applications Engineering Department](#).

**Note:** [Iris Diaphragm Mounts](#) sold separately.

## Technical Information

Outer Diameter A	Maximum Aperture B	Minimum Aperture C	Thickness D	Level Position E	Full Angular Range of Lever F	Stock No.
10mm	5mm	0.5mm	4mm	2.4mm	76°	<a href="#">#57-573</a>
						<a href="#">#57-578</a>
12mm	7mm	0.5mm	4mm	2.4mm	85°	<a href="#">#57-574</a>
						<a href="#">#57-579</a>
14.8mm	8mm	1mm	4.5mm	2.5mm	81°	<a href="#">#57-580</a>
						<a href="#">#64-507</a>
19.8mm	12mm	1mm	4mm	2.5mm	80°	<a href="#">#57-575</a>
						<a href="#">#57-581</a>
28mm	18mm	1mm	5mm	2.9mm	89°	<a href="#">#57-576</a>
						<a href="#">#57-577</a>
30mm	20mm	1.2mm	5.5mm	2.9mm	90°	<a href="#">#57-577</a>
						<a href="#">#64-508</a>

37mm	25mm	1.5mm	5.5mm	3mm	93°	<a href="#">#57-582</a>
53mm	37mm	2.5mm	6mm	3.2mm	89°	<a href="#">#57-583</a>
70mm	50mm	2.5mm	7mm	3.8mm	84°	<a href="#">#57-584</a>
82mm	60mm	4mm	8mm	4.5mm	91°	<a href="#">#57-585</a>
100mm	75mm	4mm	9mm	4.5mm	95°	<a href="#">#57-586</a>

