

TECHSPEC[®] 135mm EFL MgF₂ Coated, UV-NIR Corrected Triplet



Stock **#64-839** 1 In Stock

-

1

+

₹2,03,578

ADD TO CART

Volume Pricing	
Qty 1-5	₹2,03,578 each
Qty 6-10	₹1,73,061 each
Qty 11-25	₹1,62,862 each
Need More?	Request Quote

Product Downloads

General	
Achromatic Triplet Lens	Type:
Physical & Mechanical Properties	
22.5	Clear Aperture CA (mm):
30.00 ±0.05	Housing Diameter (mm):

20.50 ±0.05	Housing Length (mm):
Optical Properties	
135.00	Effective Focal Length EFL (mm):
±1.5 @ 248nm	Focal Length Tolerance (%):
129.31	Back Focal Length BFL (mm):
126.9	Back Focal Length BFL from Housing (mm):
CaF ₂ / Fused Silica / CaF ₂	Substrate: ☐
60-40	Surface Quality:
6.00	f/#:
0.08	Numerical Aperture NA:
MgF ₂ (193-1000nm)	Coating:
MgF ₂ @600nm	Coating Specification:
135.00	Effective Focal Length EFL @ 248nm (mm):
193 - 1000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 205:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

• Calcium Fluoride and UVFused Silica Elements


• Broadband Color-Corrected Design from 193nm to 1000nm

• Ideal for Fluorescence and Spectroscopy Applications

TECHSPEC® UV-to-NIR Corrected Triplet Lenses provide a consistent focal length (see chromatic shift information below) for wavelengths ranging from 193nm to 1000nm. These lenses were designed with broadband applications in mind. Manufactured with premier grades of Calcium Fluoride and Fused Silica, these infinite-conjugate triplets are perfect for imaging applications utilizing a wide spectrum of wavelengths. TECHSPEC® UV-to-NIR Corrected Triplet Lenses are typically used for fluorescence research in which the emitted light is in the visible and near infrared regions of the spectrum or in dual-pass systems in which the same lens is used to illuminate the excitation material as well as collect the emissions from it. Elements are uncoated and mounted in a 30mm diameter aluminum housing. Antireflection coatings available, however a minimum order quantity will apply.

Full [prescription](#) information available.

Technical Information



Effective Focal Length EFL	193 - 400nm	400 - 1000nm	193 - 1000nm
----------------------------	-------------	--------------	--------------

	Chromatic Shift	RMS Spot Size	Chromatic Shift	RMS Spot Size	Chromatic Shift	RMS Spot Size
36mm	1.8mm	240µm	0.4mm	214µm	2.2mm	268µm
45mm	1.1mm	88µm	0.3mm	69µm	1.3mm	95µm
90mm	2.0mm	64µm	0.6mm	38µm	2.5mm	69µm
135mm	1.6mm	49µm	0.6mm	31µm	2.1mm	51µm
180mm	1.4mm	46µm	0.6mm	28µm	1.9mm	45µm

;