

12mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-684



Stock **#68-683** 3 In Stock

[Similar Products](#)

- 1 + ₹1,43,100

ADD TO CART

Volume Pricing	
Qty 1+	₹1,43,100 each
Need More?	Request Quote

Product Downloads

General

Series:

ltra High Resolution Fixed Focal Length Lenses

Type:

Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:

Variable	
Length (mm):	52.50
Maximum Diameter (mm):	33.0
Outer Diameter (mm):	33

Weight (g):	105.00
-------------	--------

Optical Properties

Field of View @ Min Working Distance (mm):	58.4
Horizontal Field of View, 1/2" Sensor:	58.4mm - 28.9°

Maximum Image Circle (mm):	11.00
Focal Length FL (mm):	12.00

Working Distance (mm):	100 - ∞
Aperture (f/#):	f/1.8 - f/11

Maximum Distortion (%):	<-0.12%
Lens Wavelength Range:	VIS

Sensor

Maximum Sensor Format:	2/3"
Pixel Size (µm):	2.40

Threading & Mounting

Filter Thread:	M25.5 x 0.50
Mount:	C-Mount

Regulatory Compliance

RoHS 2015:	Exempt
Certificate of Conformance:	View
REACH 241:	Contains SVHC(s)
Country of Origin:	Japan
Imported By:	Edmund Optics India Private Limited

Product Details

- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 2.4µm Pixel Size Sensors
- Spectral Range of 400 - 1000nm
- 5mm to 50mm Focal Lengths

Ultra High Resolution Fixed Focal Length Lenses are designed to provide 10 MegaPixel resolution on axis. These lenses have a spectral range of 400 to 1000nm. Through the use of a floating focus and aspheric lens elements, these high-resolution lenses are able to maintain excellent performance from 100mm to infinity. Ultra High Resolution Fixed Focal Length Lenses feature locking focus, iris rings, and a front filter thread to allow the use of standard optical filters for increased versatility. The lenses are available in 7 focal length options and feature very low distortion.