

**TECHSPEC® 12mm Focal Length, UAV Series Fixed Focal Length Lens**



12mm Focal Length, UAV Series Fixed Focal Length Lens



Stock #22-835 **NEW** [CONTACT US](#)

- 1 + MRP ₹62,734

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹62,734 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

UAV Series	<b>Product Family:</b>
Fixed Focal Length Lens	<b>Type:</b>
Infinite Conjugate	<b>Imaging Lens Type:</b>

## Physical & Mechanical Properties

Variable Iris Option:

59.60 Length (mm):

43.50 Maximum Diameter (mm):

43.50 Outer Diameter (mm):

131 Weight (g):

4.4 Maximum Rear Protrusion (mm):

59.60 Maximum Length (mm):

59.60 Minimum Length (mm):

## Optical Properties

65.1° Horizontal Field of View @ Max Sensor Format:

65.1° Horizontal Field of View, 1.2" Sensor:

60.9° Horizontal Field of View, 1.1" Sensor:

55.6° Horizontal Field of View, 1" Sensor:

39.3° Horizontal Field of View, 2/3" Sensor:

32.5° Horizontal Field of View, 1/1.8" Sensor:

19.30 Maximum Image Circle (mm):

0.004302 Numerical Aperture NA, Object Side:

11 (9) Number of Elements (Groups):

425 - 675 Wavelength Range (nm):

12.00 Focal Length FL (mm):

500 - ∞ Working Distance (mm):

2.8 - 16 Aperture (f/#):

425 - 675 BBAR Coating:

425 - 675 BBAR Coating Specification:

14.233 Entrance Pupil Position (mm):

-4.52 Object Space Principal Plane (mm):

1.80 Image Space Principal Plane (mm):

5.30 Maximum Distortion (%):

-44.290 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

VIS Wavelength:

## Sensor

1.2" Maximum Sensor Format:

2.74 Pixel Size (µm):

## Threading & Mounting

M42.0 X 0.50 (Male) Filter Thread:

Front Thread:  
M42.0 X 0.50

Mount:  
C-Mount

## Environmental & Durability Factors

Storage Temperature (°C):  
-20 to +60 For questions regarding operating temperature please contact our support team

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

Country of Origin:  
China

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000



## Product Details

- Compact, Infinite Conjugate Lens Ideal for Photogrammetry
- 8mm, 12mm, 16mm, 25mm, and 35mm Focal Lengths
- 1.2", C-Mount Lens
- Up to 24.4 MegaPixels, 2.7µm Pixel Size Sensors



TECHSPEC® UAV Series Fixed Focal Length Lenses are compact, lightweight infinite conjugate lenses designed for the 4th Generation Sony Pregius 1.2" IMX530 and IMX540 sensors for mounting on autonomous vehicles and drones. These lenses are designed with a low Ground Separation Distance (GSD) to enable accurate survey results, and are available in 8mm, 12mm, 16mm, 25mm, and 35mm focal length options. The f/2.8 aperture provide increased light throughput and high-resolution performance. TECHSPEC® UAV Series Fixed Focal Length Lenses are C-Mount and feature a locking focus and iris rings to prevent unwanted adjustments, as well as a front filter thread for integrating standard [optical filters](#). These lenses are ideal for Drone Mapping and Surveying, Aerial Imaging, and Photogrammetry applications.

**Note:** Call for OEM Quantity and Pricing


## Technical Information




#22-835 - 12mm Focal Length, UAV Series Fixed Focal Length Lens, Relative Illumination Plot



#22-835 - 12mm Focal Length, UAV Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, Infinity Working Distance, f2.8



Legend: 0.4861, 0.5876, 0.6563



#22-835 - 12mm Focal Length, UAV Series Fixed Focal Length Lens, Distortion Plot

