

[See all 4 Products in Family](#)

12" x 12", 0.010" FL, Lenticular Array



Stock **#43-029** **12 In Stock**

- 1 + MRP ₹14,630

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹14,630 each
Qty 11-49	₹13,217 each
Need More?	Request Quote

Product Downloads

General

Type:
Lens Array

Number of Lenses:
142 per 25.4mm

Physical & Mechanical Properties

Center Thickness CT (inches):
0.06

Center Thickness CT (mm):

1.50

Dimensional Tolerance (inches):

±0.05

Dimensions (inches):

12 x 12

Dimensions (mm):

304.8 x 304.8

Effective Size (inches):

12 x 12

Thickness Tolerance (%):

±40

Thickness Tolerance (mm):

±0.6

Optical Properties

Effective Focal Length EFL (mm):

0.25

Substrate:

Acrylic

Coating:

Uncoated

Wavelength Range (nm):

400 - 1100

Effective Focal Length EFL (inches):

0.01

Index of Refraction (n_d):

1.49

Environmental & Durability Factors

Operating Temperature (°C):

80 (Maximum)

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 242:

[Compliant](#)

Country of Origin:

United States

Imported By:


Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details


- Arrays of Conventional Cylinder Lenses
- Used as High-Efficiency Diffusers
- Cylindrical Axis of Lenslet is Aligned Along the First Dimension

Lenticular Arrays consist of an array of conventional cylindrical lenses which efficiently divide, focus, and diffuse light rays. The focal length of each cylindrical lenslet is typically 3 to 5 times its width and its axis is aligned along the first dimension specified under array dimensions. Lenticular Arrays are ideal for use as high-efficiency diffusers within short working distances, projection screens and stereoscopic (3D) photography.

Technical Information



Typical Transmission of Plastic Windows



;