

1.5 OD, 12.7mm Dia., Reflective Neutral Density Filter



Stock #27-922 CLEARANCE [CONTACT US](#)

⊖ 1 ⊕ **₹1,736**

[ADD TO CART](#)

Qty 1+

₹1,736

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.70 ±0.3

Optical Density OD (Average):
1.5

Substrate:
Borosilicate

Coating:
Metallic Based ND

Thickness (mm):
1.00

Thickness Tolerance (mm):
±0.25

Transmission (%):
3.00

Type:
Neutral Density Filter

Parallelism (arcmin):
±3

Dimensional Tolerance (mm):
±0.3

Clear Aperture (%):
>90

Optical Density Tolerance (%):
±10

Regulatory Compliance

Reach 181:
[Compliant](#)

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)