

TECHSPEC<sup>®</sup> 1.5 OD 25mm Dia., NIR ND Filter



Near-IR (NIR) Neutral Density (ND) Filters

Stock **#47-532** **5 In Stock**

-

1

+

₹8,486

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹8,486 each                   |
| Qty 6-25       | ₹6,773 each                   |
| Qty 26-49      | ₹6,423 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Neutral Density Filter

Type:

Physical & Mechanical Properties

25.00 +0.0/-0.2

Diameter (mm):

3.00 ±0.10


Thickness (mm):

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| 80                                  | Clear Aperture (%):                 |
| <5                                  | Parallelism (arcsec):               |
| Optical Properties                  |                                     |
| 1.5                                 | Optical Density OD (Average):       |
| Fused Silica (Corning 7980)         | Substrate: <input type="checkbox"/> |
| Metallic Based ND                   | Coating:                            |
| 40-20                               | Surface Quality:                    |
| 3.2                                 | Transmission (%):                   |
| 700 - 1100                          | Blocking Wavelength Range (nm):     |
| λ/4                                 | Transmitted Wavefront, P-V:         |
| ±10                                 | Optical Density Tolerance (%):      |
| Regulatory Compliance               |                                     |
| Compliant                           | RoHS 2015:                          |
| View                                | Certificate of Conformance:         |
| Compliant                           | REACH 241:                          |
| United States                       | Country of Origin:                  |
| Edmund Optics India Private Limited | Imported By:                        |

## Product Details

- Ideal for NIR Wavelengths 700-1100nm
  - Optical Densities Ranging from 0.3 to 3.0
- TECHSPEC® Near-IR (NIR) Neutral Density (ND) Filters feature a spectrally flat region between 700 and 1100nm, outstanding parallelism, and exceptional surface characteristics. The combination of high tolerance and broadband performance makes our filters ideal for attenuating a wide range of IR sources. The UV Fused Silica substrate features a low coefficient of thermal expansion and excellent surface quality, making these filters suitable for attenuating low power lasers, including lasers at the 1064nm Nd:YAG wavelength. Other applications include NIR spectroscopy, machine vision, and analytical chemistry. TECHSPEC Near-IR (NIR) Neutral Density (ND) Filters may be stacked to obtain a variety of optical densities. Orient the mirrored side toward the source at a 0° angle of incidence. Optical Densities of 0.5, 1.0, 1.5, 2.0, 2.5, and 3.0 are available in a [Pre-Loaded Filter Wheel](#).
- Note:** Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact [kits@edmundoptics.com](mailto:kits@edmundoptics.com).

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

# Compatible Mounts

;