

LightPath 354220 | 1310nm Alignment, 0.25 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#47-220**

10 TO 12 DAYS

-

1

+

₹15,660.00

ADD TO CART

Qty 1-10
₹15,660.00
Qty 11+
₹13,790.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.25

Substrate: D-ZK3
Coating: BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.50
f#: 2.00
Bevel: Protective bevel as needed
Connector: FC/PC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 17.1
Lightpath Lens Code: 354220
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 1050 - 1600
Conjugate Distance: Infinite
Lens Included: #87-119
Alignment Wavelength (nm): 1310

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant