

[See all 159 Products in Family](#)

TECHSPEC® 1350nm CWL, 50mm Dia. Hard Coated OD 4.0 50nm Bandpass Filter



Stock **#85-911** **4 In Stock**

[Additional Bandwidths](#)

- 1 + MRP ₹87,270

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-5	₹87,270 each
Qty 6-25	₹69,816 each
Qty 26-49	₹65,453 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter **Type:**

Physical & Mechanical Properties

50.00 +0.0/-0.1 **Diameter (mm):**

Clear Aperture CA (mm):

Construction:

Mounted in Black Anodized Ring

Physical Durability:

Adhesion per MIL-PRF-13830B, Section C.4.5.12
 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11
 Cleaning per MIL-C-48497A Section 4.5.4.2

Substrate Thickness (mm):

3.5±0.5

Optical Properties**Angle of Incidence (°):**

0

Bandwidth (nm):

45

Optical Density OD (Average):

≥4.0

Center Wavelength CWL (nm):

1,350.00

Full Width-Half Max FWHM (nm):

50.00

Substrate:

Optical Glass

Minimum Transmission (%):

≥90

Coating:

Hard Coated

Surface Quality:

80-50

Blocking Wavelength Range (nm):

200 - 1800

Threading & Mounting**Mount Thickness (mm):**

5.0±0.1

Environmental & Durability Factors**Environmental Durability:**

Humidity per ML-STD-810H, Section 507.6
 Temperature per ML-STD-810H, Section 501.7 and 502.7

Regulatory Compliance**RoHS 2015:**

Compliant

Certificate of Conformance:[View](#)**Reach 247:**

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Transmission, Deep Blocking
- Broad Bandwidths Ideal for Imaging Applications
- Available in VIS and IR Center Wavelengths
- [Hard Coated OD 4.0 10nm](#) and [25nm](#) Bandpass Filters Also Available

TECHSPEC® Hard Coated OD 4.0 50nm Bandpass Filters are ideal for imaging applications, including machine vision inspection, fluorescence microscopy, and a variety of biotech instrumentation. These bandpass filters eliminate

unwanted background noise and enhance the signal-to-noise ratio within imaging applications. Unlike traditional filters, these hard coated filters are fabricated using only a single substrate. TECHSPEC® Hard Coated OD 4.0 50nm Bandpass Filters offer deeper blocking, higher transmission, and steeper slopes than traditional coated filters. Hard Coated OD 4.0 [10nm](#) and [25nm](#) are also available.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Technical Information



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

Compatible Mounts
