

TECHSPEC[®] 150mm Dia., 0.50 Numerical Aperture VIS Coated, Aspheric Lens



Stock #22-711 4 In Stock

[Other Coating Options](#)

-

1

+

₹1,77,109

ADD TO CART

Volume Pricing	
Qty 1-5	₹1,77,109 each
Qty 6+	₹1,41,687 each
Need More?	Request Quote

Product Downloads

General

Type:
Aspheric Lens

Physical & Mechanical Properties

Diameter (mm):
150.00 +0.0/-0.1

Centering (arcmin):
≤5

Clear Aperture CA (mm):

128	
	Edge Thickness ET (mm):
7.51	
	Center Thickness CT (mm):
48.30 ±0.1	
	Bevel:
Protective as needed	

	Shape of Back Surface:
Plano	

Optical Properties

	Effective Focal Length EFL (mm):
150.00 @ 587.6nm	
	Numerical Aperture NA:
0.50	

	Back Focal Length BFL (mm):
118.16	
	Substrate:
N-BK7	

	Asphere Figure Error, RMS @ 632.8nm:
1.2λ	
	Coating:
BBAR (425-675nm)	

	Coating Specification:
R _{avg} ≤1.5% @ 425 - 675nm	
	Surface Quality:
60-40	

	f/#:
1.00	
	Wavelength Range (nm):
350 - 2200	

	Conjugate Distance:
Infinite	
	Power (diopters):
6.67	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

	Reach 250:
Compliant	
	Country of Origin:
Singapore	

	Imported By:
Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Diameters from 10 to 200mm
- Focal Lengths from 7.5 to 300mm
- Broadband AR Coatings Available

TECHSPEC® Aspheric Lenses are designed to focus light while eliminating spherical aberration from divergent light sources in applications including focusing the output of a laser diode. [Aspheric lenses can increase the numerical aperture of a lens while minimizing system aberrations](#). Aspheric lenses may also reduce the number of elements needed in a multi-element system. Aspheric lenses can reduce overall system weight while providing advantages such as increasing throughput or simplifying assembly.

TECHSPEC Aspheric Lenses feature low f/#'s for optimum light gathering performance. Prescription data is available to easily integrate these aspheric lenses into an optical system. These lenses have also been computer optimized to eliminate spherical aberration while minimizing higher order aberrations. MS coating option provides less than 1.5% reflection from 425 – 675nm. NIR coating option provides less than 1.5% reflection from 600 – 1050nm. Contact our sales department for volume pricing or for help specifying a custom aspheric lens.

Technical Information



;