


[See all 8 Products in Family](#)

13mm² DUV Photodiode with Metal Housing



DUV Photodiodes

Stock **#84-983** **2 In Stock**

MRP ₹10,673

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹10,673 each
Qty 5-9	₹9,399 each
Qty 10-24	₹8,337 each
Need More?	Request Quote

Product Downloads

General

0.5@0V, 1 kΩ **Rise Time (μs):**

Physical & Mechanical Properties

3.6x3.6 **Size of Active Area (mm):**

Active Area (mm²):

Optical Properties

980.00 **Peak Response Wavelength (nm):**

Electrical

0.5 **Responsivity @ 980nm (AW):**

Minimum: 0.2
Typical: 0.8 **Shunt Resistance @ V=-10mV (GΩ):**

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

150.00 **Capacitance @ V_R=0V (pF):**

4.1×10^{-14} **Noise Equivalent Power NEP (W/ Hz^{1/2}):**
@ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

Hardware & Interface Connectivity

TO-5 **Connector:**

Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-55 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Malaysia **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.