See all 413 Products in Family

# TECHSPEC® 15.0mm Dia. x 18.0mm FL, VIS-NIR, Inked, Plano-Convex Lens

Stock **#49-918-INK** CONTACT US

Other Coating Options

- 1 + MRP ₹6,584

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|---|---|
| Qty 1-9 | **₹6,584** each |
| Qty 10-24 | **₹5,947** each |
| Qty 25-49 | **₹5,284** each |
| Need More? | Request Quote |

Product Downloads

## General

**Type:**

Plano-Convex Lens

## Physical & Mechanical Properties

**Diameter (mm):**

15.00 ±0.025

**Centering (arcmin):**
<1

**Center Thickness CT (mm):**
4.00 ±0.10

**Edge Thickness ET (mm):**
1.40

**Clear Aperture CA (mm):**
14

**Bevel:**
Protective as needed

## Optical Properties

**Effective Focal Length EFL (mm):**
18.00 @ 587.6nm

**Back Focal Length BFL (mm):**
15.61

**Coating:**
VIS-NIR (400-1000nm)

**Coating Specification:**
$R_{abs}$ ≤0.25% @ 880nm
$R_{avg}$ ≤1.25% @ 400 - 870nm
$R_{avg}$ ≤1.25% @ 890 - 1000nm

**Substrate:**
N-SF5

**Surface Quality:**
40-20

**Power (P-V) @ 632.8nm:**
1.5λ

**Irregularity (P-V) @ 632.8nm:**
λ/4

**Focal Length Tolerance (%):**
±1

**Radius $R_1$ (mm):**
12.11

**f/#:**
1.2

**Numerical Aperture NA:**
0.42

**Wavelength Range (nm):**
400 - 1000

**Damage Threshold, By Design:**
5 J/cm$^2$ @ 532nm, 10ns

## Regulatory Compliance

**Certificate of Conformance:**
View

**Country of Origin:**
Japan

**Imported By:**
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our custom manufacturing capabilities or submit an inquiry here.

# Product Details

- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: Uncoated, $MgF_2$, VIS 0°, NIR I, NIR II, VIS-EXT, and YAG-BBAR

TECHSPEC® VIS-NIR Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters,

detectors, lasers, and fiber optics. Plano-Convex lenses are ideal for a multitude of optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. TECHSPEC® VIS-NIR Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered **uncoated** or with broadband anti-reflective (BBAR) coatings, which include **MgF2**, **VIS 0°**, **NIR I**, **NIR II**, **VIS-EXT**, and **YAG-BBAR**.

These coated lenses are optimized for a wide range of optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

# Technical Information







| N-BK7 | |
|---|---|
|  | Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.<br>**Click Here to Download Data** |
|  | Typical transmission of a 3mm thick N-BK7 window with MgF2 (400-700nm) coating at 0° AOI.<br>The blue shaded region indicates the coating design wavelengh range, with the following specification:<br>$R_{avg} \leq 1.75\%$ @ 400 - 700nm (N-BK7)<br>Data outside this range is not guaranteed and is for reference only.<br>**Click Here to Download Data** |
|  | Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.<br>The blue shaded region indicates the coating design wavelengh range, with the following specification:<br>$R_{avg} \leq 0.5\%$ @ 350 - 700nm<br>Data outside this range is not guaranteed and is for reference only.<br>**Click Here to Download Data** |




Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 0.25\%$ @ 880nm
$R_{avg} \leq 1.25\%$ @ 400 - 870nm
$R_{avg} \leq 1.25\%$ @ 890 - 1000nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{avg} \leq 0.4\%$ @ 425 - 675nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 0.25\%$ @ 532nm
$R_{abs} \leq 0.25\%$ @ 1064nm
$R_{avg} \leq 1.0\%$ @ 500 - 1100nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{avg} \leq 0.5\%$ @ 600 - 1050nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 1.5\%$ @ 750 - 800nm
$R_{abs} \leq 1.0\%$ @ 800 - 1550nm
$R_{avg} \leq 0.7\%$ @ 750 - 1550nm

Data outside this range is not guaranteed and is for reference only.

**Click Here to Download Data**

## Coating Curves

## Compatible Mounts

;