

TECHSPEC[®] 15mm Dia 0.30 NA, UV Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock #33-952 14 In Stock

[Other Coating Options](#)

-

1

+

₹38,536

ADD TO CART

Volume Pricing	
Qty 1-5	₹38,536 each
Qty 6-25	₹30,829 each
Qty 26-49	₹28,882 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General


Aspheric Lens	Type:
Physical & Mechanical Properties	
15.00 +0.0/-0.1	Diameter (mm):
≤5	Centering (arcmin):
13.5	Clear Aperture CA (mm):
1.79	Edge Thickness ET (mm):
4.36 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
25.00 @ 587.6nm	Effective Focal Length EFL (mm):
0.30	Numerical Aperture NA:
22.01	Back Focal Length BFL (mm):
Fused Silica (Corning 7980)	Substrate: ☐
587.6	Aspheric Design Wavelength (nm):
1.2λ	Asphere Figure Error, RMS @ 632.8nm:
UV (250-425nm)	Coating:
R _{avg} ≤1.5% @ 250 - 425nm	Coating Specification:
60-40	Surface Quality:
1.67	f/#:
250 - 425	Wavelength Range (nm):
Infinite	Conjugate Distance:
40.00	Power (diopters):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Low Coefficient of Thermal Expansion
- Precision and High Precision Options
- High Numerical Apertures to Maximize Throughput

TECHSPEC® UV Fused Silica Aspheric Lenses offer the benefits of an aspheric element combined with the manufacturing precision of state-of-the-art grinding and polishing equipment. These fused silica optics can be easily designed and integrated into complex optical systems with the available prescription data. Featuring low *f*/#'s, which allow for a larger aperture and thus more light gathering and focusing performance, these fused silica lenses are computer-optimized to eliminate spherical and minimize higher order aberrations. TECHSPEC® UV Fused Silica Aspheric Lenses offer a low coefficient of thermal expansion, making them ideal for applications in metrology, beam-focusing or collimating, and OEM integration. These lenses are available in a variety of coating options and are offered in sizes ranging from 10-50mm.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS