

[See all 6 Products in Family](#)

1550nm CWL, 25mm Dia., OD 4 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock #12-514 **4 In Stock**

- 1 + ₹1,66,210

ADD TO CART

Volume Pricing	
Qty 1-9	₹1,66,210 each
Qty 10-25	₹1,52,352 each
Qty 26-49	₹1,42,699 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter **Type:**

Filter Design: Multi-Cavity **Note:**

Physical & Mechanical Properties

25.00	Diameter (mm):
21.34	Clear Aperture CA (mm):
Mounted in Black Anodized Ring	Construction:
2.00	Substrate Thickness (mm):
Optical Properties	
0	Angle of Incidence (°):
4.00	Optical Density OD (Average):
1,550.60	Center Wavelength CWL (nm):
2.00	Full Width-Half Max FWHM (nm):
Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>
>90	Minimum Transmission (%):
Hard Coated	Coating:
T _{abs} >90% @ 1550.6nm	Transmission (%):
900 - 1533, 1569 - 1650	Blocking Wavelength Range (nm):
Threading & Mounting	
5.00 ±0.05	Mount Thickness (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- >90% Transmission at Design Wavelength
- Up to >OD 8 Blocking Across Blocking Range
- As Narrow as <0.5nm Full Width-Half Max

Ultra Narrow Hard Coated Bandpass Filters are ideal for use as laser line, laser cleanup, or laser excitation filters in demanding medical and laser applications. These hard coated narrowband filters are manufactured with state of the art plasma deposition processes, which ensure high resistance to laser damage and a high level of performance over a long period of time. Depending on the wavelength range and system requirements, these Ultra Narrow Hard Coated Bandpass Filters will provide up to 98% peak transmission, up to OD 10 blocking by design, center wavelength tolerances as tight as 0.05nm, FWHM bandwidths <1nm, and extremely steep edges with an ultra-flat passband profile. Typical applications for these ultra narrowband filters include fluorescence microscopy, flow cytometry, real time DNA sequencing, and polymerase chain reaction (PCR) diagnostic instruments.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Technical Information



Compatible Mounts