


TECHSPEC® 30 x 30mm $\lambda/10$ ZERODUR® Uncoated Mirror Substrate



Stock #71-517 **1 In Stock**

MRP ₹12,914

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹12,914 each |
| Qty 6-25 | ₹10,331 each |
| Need More? | Request Quote |

Product Downloads

General

Mirror Substrate **Type:**

Physical & Mechanical Properties

5.00 ±0.20 **Thickness (mm):**

30.0 x 30.0 +0.00/-0.20 **Dimensions (mm):**

Back Surface:

Commercial Polish

Bevel:

Protective as needed

Clear Aperture (%):

90

Edges:

Ground

Length (mm):

30.00

Width (mm):

30.00

Parallelism (arcsec):

30

Optical Properties

Coating:

Uncoated

Surface Flatness (P-V):

$\lambda/10$

Substrate:

ZERODUR®

Surface Quality:

20-10

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):

0.1

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Vietnam

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Precision ZERODUR® Substrates
- $\lambda/10$ Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR Mirror Substrates are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR Mirror Substrates feature precision polished substrates with $\lambda/10$ flatness and 20-10 surface quality.