

TECHSPEC[®] 15mm 355nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock **#37-649** 3 In Stock

-

1

+

₹23,130

ADD TO CART

Volume Pricing	
Qty 1-5	₹23,130 each
Qty 6-25	₹18,450 each
Qty 26-49	₹17,370 each
Need More?	Request Quote

Product Downloads


General	
Right Angle Mirror	Type:
Physical & Mechanical Properties	
15.00	Length of Legs (mm):
+0.00/-0.10	Dimensional Tolerance (mm):

Protective as needed	Bevel:
90	Clear Aperture (%):
21.20	Length of Hypotenuse (mm):
Optical Properties	
λ /20	Surface Flatness (P-V):
Fused Silica (Corning 7980)	Substrate: ☐
20-10	Surface Quality:
Coating Specification: R _{abs} >99.8% @ 355nm @45° AOI R _{avg} >99.5% @ 351 - 358nm @45° AOI	
Laser Mirror (355nm)	Coating:
355	Design Wavelength DWL (nm):
±1	Pyramid Tolerance (arcmin):
±15	Angle Tolerance (arcsec):
Damage Threshold, Reference: ☐ 1MW/cm² @ 355nm	
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- >99.5% Reflectivity at the Design Wavelength
- ±15 Arcsecond Angular Tolerance
- High Thermal Stability Substrates

TECHSPEC® Laser Line λ /20 High Tolerance Right Angle Mirrors are designed at Nd:YAG wavelengths with durable, high reflectivity dielectric coatings. Right angle mirrors are easily mounted and integrated into systems that redirect light 90°. With ±15 arcsecond angular tolerance and ±1 arcminute pyramid tolerance, these laser line mirrors simplify alignment when mounting. TECHSPEC® Laser Line λ /20 High Tolerance Right Angle Mirrors feature laser induced damage threshold specifications making them ideal for demanding laser applications.



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).