

TECHSPEC[®] 15mm Dia. 400 - 750nm Broadband λ /4 Mirror



Broadband Dielectric λ /4 Mirrors

Stock #70-669 15 In Stock

-

1

+

₹6,072

ADD TO CART

Volume Pricing	
Qty 1-5	₹6,072 each
Qty 6-25	₹4,866 each
Qty 26-49	₹4,554 each
Need More?	Request Quote

Product Downloads

General	
Flat Mirror	Type:
Physical & Mechanical Properties	
15.00 +0.00/-0.25	Diameter (mm):
Commercial Polish	Back Surface:

90	Clear Aperture (%):
13.50	Clear Aperture CA (mm):
Ground	Edges:
5	Parallelism (arcmin):

2.00 ±0.25	Thickness (mm):
------------	-----------------

Optical Properties

Dielectric Mirror (400-750nm)	Coating:
Coating Specification: R _{avg} >98% @400 - 750nm (0-45°, All Polarizations) R _{avg} >99% @400 - 750nm (0-45°, S-Polarizations)	

400 - 750	Wavelength Range (nm):
-----------	------------------------

λ/4 (typical)	Surface Flatness (P-V):
---------------	-------------------------

BOROFLOAT®	Substrate: □
------------	--------------

60-40	Surface Quality:
-------	------------------

Dielectric	Coating Type:
------------	---------------

0-45	Angle of Incidence (°):
------	-------------------------

0.5 J/cm ² @ 532nm, 20ns, 20Hz	Damage Threshold, By Design: □
---	--------------------------------

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

United States	Country of Origin:
---------------	--------------------

Edmund Optics India Private Limited	Imported By:
-------------------------------------	--------------

Product Details

- Enhanced Reflectivity and LDT over Metallic Coatings
- Average Reflectivity >99% from 400 – 750nm
- Designed for all Polarization States at 0 – 45° AOI
- λ/10 Versions Available

TECHSPEC® Broadband Dielectric λ/4 Mirrors feature a high laser damage threshold of 0.5 J/cm² @ 532nm, 20ns pulse, at 20Hz as well as a >99% reflection from 400 – 750nm across all polarization states. Constructed from highly durable BOROFLOAT® substrates, these mirrors feature outstanding thermal and high chemical durability making them ideal for high temperature and harsh environment applications. TECHSPEC® Broadband Dielectric λ/4 Mirrors are available in a variety of diameters from 12.5 - 50mm. A low-cost alternative to our precision polished [TECHSPEC Broadband Dielectric λ/10 Mirrors](#), these mirrors are ideal for spectroscopy, microscopy, and general laboratory use such as beam steering or reflection applications utilizing multiple laser sources.

Note: Surface Flatness is measured pre-coating and deviations may appear after the coating has been applied. For applications where surface flatness is critical it is recommended it is recommended to use the [TECHSPEC® Broadband Dielectric λ/10 Mirrors](#).