

[See all 75 Products in Family](#)

TECHSPEC® 15mm Dia., 0.5 NA, Uncoated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock **#18-749** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹65,478

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹65,478 each
Qty 6-10	₹58,920 each
Qty 11-25	₹54,986 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

15.00 +0.00/-0.10 **Diameter (mm):**

Centering (arcmin):

<5

13.5 Clear Aperture CA (mm):

3.31 Edge Thickness ET (mm):

8.00 ±0.10 Center Thickness CT (mm):

Protective as needed Bevel:

Convex Shape of Back Surface:

Optical Properties

15.00 @2000nm Effective Focal Length EFL (mm):

0.50 Numerical Aperture NA:

10.303 Back Focal Length BFL (mm):

N-FK58 Substrate:

2000 Aspheric Design Wavelength (nm):

1.2λ Asphere Figure Error, RMS @ 632.8nm:

Uncoated Coating:

60-40 Surface Quality:

1 f#:

335 - 2500 Wavelength Range (nm):

Infinite Conjugate Distance:

2000 Focal Length Specification Wavelength (nm):

66.67 Power (diopters):

Regulatory Compliance

[View](#) Certificate of Conformance:

Singapore Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Optimized for Applications in the NIR
- Uncoated or AR coated versions available
- Multiple Design Wavelengths Available

TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are optimized to eliminate spherical aberration in the near-infrared. Manufactured from S-LAH64 or N-BK7 substrates and polished through a computer numerical controlled (CNC) process, these aspheric lenses achieve high precision performance across the NIR spectrum. These NIR aspheric lenses include uncoated substrates designed at 780nm with coating options at 350-700nm, 600-1050nm, or 900-1700nm. TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are available with low numerical aperture designs for applications that require beam shape to be maintained as well as high numerical aperture designs for light-gathering applications. For custom designed CNC polished aspheric lenses, please contact us.

Compatible Mounts
