


[See all 14 Products in Family](#)

15mm Dia. NIR Linear Polarizing Film



Stock #18-938 CLEARANCE **8 In Stock**

₹5,539

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,539 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Protective Film on Both Sides **Note:**

Physical & Mechanical Properties

15.00 **Diameter (mm):**

0.50 ±0.1 **Thickness (mm):**

±0.25 Dimensional Tolerance (mm):

Polarizing Film Construction:

Optical Properties

Uncoated Coating:

400:1 (Average @ 800 - 2200nm) Extinction Ratio:

Polymer Film on TAC Substrate:

Single: 29 (400 - 760 nm), 39 (761 - 2200nm)
Crossed: 0.02 (400 - 760nm), 0.11 (761 - 2200nm) Transmission (%):

400 - 2200 Wavelength Range (nm):

99.83 @ 400 - 760nm
99.63 @ 761 - 2200nm Polarization Efficiency (%):

29 @ 400 - 760nm
39 @ 761 - 2200nm Transmission, Single (%):

0.02 @ 400 - 760nm
0.11 @ 761 - 2200nm Transmission, Crossed (%):

Environmental & Durability Factors

Heat Resistance 85°C Dry
Cold Resistance -55°C Operating Temperature (°C):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 240:

United States Country of Origin:

Edmund Optics India Private Limited Imported By:


Product Details

- Ideal for NIR Polarization Applications
- >400:1 Extinction Ratio from 800 - 2200nm
- High Efficiency Across Wavelength Range
- Durable Polymer Substrate


Near-Infrared (NIR) Linear Polarizing Film consists of a durable polymer substrate and is ideal for imaging applications that range from the visible to NIR (400 - 2200nm). This polarizing polymer film features an excellent average transmission of 39% with greater than 99.6% polarization efficiency for incident randomly polarized light between 760 and 2200nm. Multiple rectangular sizes are available to accommodate light sources that range from low power NIR lasers with small beam diameters, to larger LED light beams. Near-Infrared (NIR) Linear Polarizing Film is used in industrial imaging and laboratory applications, i.e. to attenuate the intensity of low output NIR lasers and LEDs or to reduce glare in images recorded using NIR photodetectors. The polarization axis is labelled on the protective masking of the polarizing polymer film for rectangular parts and as a notch cutout on the polarizing polymer film for circular parts.

Note: Remove protective masking before first use.

Technical Information



NIR Linear Polarizing Film



;