

[See all 5 Products in Family](#)

15mm Dia. x 15mm EFL Arton Plastic Asphere, Coated



Stock #90-324 CLEARANCE **20+ In Stock**

MRP ₹2,421

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,421 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

15.00 **Diameter (mm):**

12.00 **Clear Aperture CA (mm):**

3.9 **Edge Thickness ET (mm):**

Protective as needed	Bevel:
12.79	Flange Distance (mm):
Optical Properties	
15.00 ±0.2	Effective Focal Length EFL (mm):
0.40	Numerical Aperture NA:
12.79	Back Focal Length BFL (mm):
Arton Plastic	Substrate: □
BBAR (650-850nm)	Coating:
R _{abs} <1.0% @ 650 - 850nm	Coating Specification:
1.25	f#:
57.0	Abbe Number (v_d):
650 - 850	Wavelength Range (nm):
Infinite	Conjugate Distance:


Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Superior Durability for Harsh Environments
- High Heat Resistance
- Low Water Absorbency

Arton® Plastic Aspheric Lenses are ideal alternatives to PMMA or polycarbonate plastic aspheric lenses for weight sensitive, harsh environment applications. Typical plastic substrates degrade in performance in hot or humid environments. Arton®, a polyolefin thermoplastic plastic substrate, maintains plastic's high translucency and low birefringence, while featuring increased heat resistance and decreased water absorbency.

Technical Information



Compatible Mounts