

[See all 36 Products in Family](#)

## 15mm Dia., 2mm Thick, Uncoated, Suprasil Window



Suprasil® Windows

Stock **#89-685** NEW [CONTACT US](#)

-

1

+

₹10,223

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,223 each                  |
| Qty 6-25       | ₹8,178 each                   |
| Qty 26-49      | ₹7,667 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
| Protective Window                | Type:                   |
| Physical & Mechanical Properties |                         |
| 13.5                             | Clear Aperture CA (mm): |
| 15.00 +0/-0.1                    | Diameter (mm):          |

|                      |                          |
|----------------------|--------------------------|
| 2.00 ±0.10           | Thickness (mm):          |
| Protective as needed | Bevel:                   |
| 90                   | Clear Aperture (%):      |
| Fine Ground          | Edges:                   |
| <5                   | Parallelism (arcsec):    |
| 0.17                 | Poisson's Ratio:         |
| 70                   | Young's Modulus (GPa):   |
| 591.00               | Knoop Hardness (kg/mm²): |

Optical Properties

|               |                                        |
|---------------|----------------------------------------|
| Uncoated      | Coating:                               |
| Suprasil® 300 | Substrate: <input type="checkbox"/>    |
| 1.459         | Index of Refraction (n <sub>d</sub> ): |
| 10-5          | Surface Quality:                       |
| λ/10          | Transmitted Wavefront, P-V:            |
| 67.8          | Abbe Number (v <sub>d</sub> ):         |
| 200 - 3500    | Wavelength Range (nm):                 |

Material Properties

|                                          |                                                              |
|------------------------------------------|--------------------------------------------------------------|
| 2.2                                      | Density (g/cm³):                                             |
| 0.51 (0 to +100°C)<br>0.58 (0 to +200°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Vietnam                             | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- High Transmission from 200 to 3500nm
  - <1 ppm OH Content for Minimal Absorption Losses
  - 10-5 Surface Quality and up to λ/10 TWD
- Suprasil® Windows are constructed from high purity synthetic fused silica and provide high, flat transmission from 200 to 3500nm. Suprasil has similar mechanical properties to fused silica with the added benefit of having no absorption bands in the visible or infrared spectra, resulting in no transmission loss between 1400 - 2700nm. Compared to Infrasil®, Suprasil has lower absorption with a <1 ppm OH content, causing negligible increase in temperature from bulk absorption when used with high powered lasers. Suprasil Windows are ideal for laser material processing, medical laser applications, or applications using Nd:doped or 2 micron lasers.

## Technical Information



