

TECHSPEC® 15mm Dia. x 40mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-701-INK** 17 TO 22 D= DAYS
[Other Coating Options](#)

- 1 + **₹9,309.00**

ADD TO CART

Qty 1-5
₹9,309.00
Qty 6+
₹7,439.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 ±0.025

Effective Focal Length EFL (mm):
40.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 35.63
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 14.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 7.58 ±0.20
Center Thickness CT 1 (mm) : 5.98 ±0.10
Center Thickness CT 2 (mm) : 1.60 ±0.10
Radius R₁ (mm) : 26.97
Radius R₂ (mm) : -17.64
Radius R₃ (mm) : -205.03
Edge Thickness ET (mm) : 6.38
Substrate : ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 2.67
Numerical Aperture NA : 0.19
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View