

TECHSPEC®

15mm Dia. x 22.5mm FL, NIR I Coated, Double-Convex Lens



Stock **#49-482** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹3,698.00

ADD TO CART

Qty 1-9
₹3,698.00
Qty 10+
₹3,328.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Back Focal Length BFL (mm):
21.29

Effective Focal Length EFL (mm): 22.50
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.20
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.54
Radius R₁=R₂ (mm): 34.36
Clear Aperture CA (mm): 14.00
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant