

[See all 58 Products in Family](#)

TECHSPEC<sup>®</sup> 15mm Dia. x 30mm FL, NIR I Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-210** 1 In Stock

-

1

+

₹11,911

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹11,911 each                  |
| Qty 6-25       | ₹9,498 each                   |
| Qty 26-49      | ₹8,953 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

15.00 -0.025

Diameter (mm):

|                      |                           |
|----------------------|---------------------------|
| <1                   | Centering (arcmin):       |
| 3.60 ±0.10           | Center Thickness CT (mm): |
| 1.38                 | Edge Thickness ET (mm):   |
| 14                   | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

|                                             |                                                                                                                  |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------|
| Optical Properties                          |                                                                                                                  |
| 30.00 @ 587.6nm                             | Effective Focal Length EFL (mm):                                                                                 |
| 27.53                                       | Back Focal Length BFL (mm):                                                                                      |
| NIR I (600-1050nm)                          | Coating:                                                                                                         |
| R <sub>avg</sub> ≤0.5% @ 600 - 1050nm       | Coating Specification:                                                                                           |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate:                      |
| 40-20                                       | Surface Quality:                                                                                                 |
| 3 Rings                                     | Power (P-V) @ 632.8nm:                                                                                           |
| 0.5 Rings                                   | Irregularity (P-V) @ 632.8nm:                                                                                    |
| ±1                                          | Focal Length Tolerance (%):                                                                                      |
| 13.75                                       | Radius R <sub>1</sub> (mm):                                                                                      |
| 2                                           | f/#:                                                                                                             |
| 0.25                                        | Numerical Aperture NA:                                                                                           |
| 600 - 1050                                  | Wavelength Range (nm):                                                                                           |
| 7 J/cm <sup>2</sup> @ 1064nm, 10ns          | Damage Threshold, Reference:  |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| <a href="#">Compliant</a>           | RoHS 2015:                  |
| <a href="#">View</a>                | Certificate of Conformance: |
| <a href="#">Compliant</a>           | Reach 235:                  |
| Japan                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


- AR Coated to Provide <0.5% Reflection per Surface for 600 - 1050nm
- Precision Fused Silica Substrate
- Various Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [UV-AR](#), [UV-VIS](#), [VIS-EXT](#), [VIS-NIR](#), [VIS 0°](#), [YAG-BBAR](#), and [NIR II](#)

TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses NIR I Coated feature precision specifications and a [variety of coating options](#) on a broadband substrate. Fused Silica is commonly used in applications from the Ultraviolet (UV) through the Near-Infrared (NIR). Its low index of refraction, low coefficient of thermal expansion, and low inclusion content make it ideal for laser applications and harsh environmental conditions. TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses NIR I Coated feature industry leading diameter and centration specifications, making them ideal for integration into demanding imaging and targeting applications. These lenses are NIR I coated to increase their coating performance in the 600nm to 1050nm range.

Technical Information

FUSED SILICA


Uncoated Fused Silica  
Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

Fused Silica with MgF<sub>2</sub> Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-AR Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}$$


$$R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-VIS Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.






The blue shaded region indicates the coating design wavelength range, with the following specification:



$$R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$$

$$R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

|                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <p data-bbox="569 270 1081 371"><b>Fused Silica with VIS-EXT Coating<br/>Typical Transmission</b></p>       | <p data-bbox="1346 448 1839 498">Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p data-bbox="1335 513 1850 560">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 575 1707 599"><math>R_{avg} \leq 0.5\% @ 350 - 700\text{nm}</math></p> <p data-bbox="1346 614 1839 661">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 676 1711 700"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                  |
| <p data-bbox="573 943 1089 1044"><b>Fused Silica with VIS-NIR Coating<br/>Typical Transmission</b></p>    | <p data-bbox="1346 1089 1839 1136">Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p data-bbox="1335 1151 1850 1199">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1493 1213 1692 1237"><math>R_{abs} \leq 0.25\% @ 880\text{nm}</math></p> <p data-bbox="1472 1237 1713 1261"><math>R_{avg} \leq 1.25\% @ 400 - 870\text{nm}</math></p> <p data-bbox="1472 1261 1713 1285"><math>R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}</math></p> <p data-bbox="1346 1323 1839 1371">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 1386 1711 1409"><a href="#">Click Here to Download Data</a></p> |
| <p data-bbox="569 1617 1073 1718"><b>Fused Silica with VIS 0° Coating<br/>Typical Transmission</b></p>    | <p data-bbox="1335 1795 1850 1843">Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p data-bbox="1335 1857 1850 1905">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 1920 1707 1944"><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p> <p data-bbox="1346 1958 1839 2006">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 2021 1711 2044"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                         |
| <p data-bbox="548 2288 1106 2389"><b>Fused Silica with YAG-BBAR Coating<br/>Typical Transmission</b></p>  | <p data-bbox="1346 2442 1839 2493">Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p data-bbox="1335 2507 1850 2555">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1493 2570 1692 2594"><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math></p> <p data-bbox="1493 2594 1692 2617"><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math></p> <p data-bbox="1472 2617 1713 2641"><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p data-bbox="1346 2656 1839 2703">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 2718 1711 2742"><a href="#">Click Here to Download Data</a></p>      |

|                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Fused Silica with NIR I Coating</div><div>Typical Transmission</div><div></div></div>   | <div>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}</math></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                                   |
| <div><div>Fused Silica with NIR II Coating</div><div>Typical Transmission</div><div></div></div> | <div>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{abs} \leq 1.5\% \text{ @ } 750 - 800\text{nm}</math></div><div><math>R_{abs} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}</math></div><div><math>R_{avg} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}</math></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |