

[See all 70 Products in Family](#)

TECHSPEC<sup>®</sup> 15mm Diameter, 1550nm V-Coat,  $\lambda$ /4 N-BK7 Window

See More by [SCHOTT Optical Components](#)



Stock #83-529 20+ In Stock

-

1

+

₹6,491

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹6,491 each                   |
| Qty 6-25       | ₹5,208 each                   |
| Qty 26-49      | ₹4,841 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
| Laser Line Window                | Type:                   |
| Physical & Mechanical Properties |                         |
| 13.50                            | Clear Aperture CA (mm): |
| 15.00 +0.00/-0.25                | Diameter (mm):          |

|                      |                          |
|----------------------|--------------------------|
| 3.00 ±0.20           | Thickness (mm):          |
| ≤1                   | Parallelism (arcmin):    |
| Protective as needed | Bevel:                   |
| 90                   | Clear Aperture (%):      |
| Fine Ground          | Edges:                   |
| 0.21                 | Poisson's Ratio:         |
| 82                   | Young's Modulus (GPa):   |
| 610.00               | Knoop Hardness (kg/mm²): |

|                                  |                                        |
|----------------------------------|----------------------------------------|
| Optical Properties               |                                        |
| Laser V-Coat (1550nm)            | Coating:                               |
| 1550                             | Design Wavelength DWL (nm):            |
| N-BK7                            | Substrate: <input type="checkbox"/>    |
| 1.516                            | Index of Refraction (n <sub>d</sub> ): |
| 60-40                            | Surface Quality:                       |
| 64.17                            | Abbe Number (v <sub>d</sub> ):         |
| R <sub>abs</sub> <0.25% @ 1550nm | Coating Specification:                 |
| λ/4                              | Surface Flatness (P-V):                |

|                                           |                                                              |
|-------------------------------------------|--------------------------------------------------------------|
| Material Properties                       |                                                              |
| 2.51                                      | Density (g/cm³):                                             |
| 7.1 (-30 to +70°C)<br>8.3 (+20 to +300°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 235:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at Design Wavelength
- Coatings Available for HeNe, Diode, and Nd:YAG Laser Sources
- Precision N-BK7 Substrate
- Also Available [Uncoated](#), [MgF<sub>2</sub> Coated](#) and [VIS 0° Coated](#)

TECHSPEC® λ/4 N-BK7 Laser Line Windows are ideally suited for industrial and low power laser applications. The high tolerance design yields minimal beam distortion and scatter. Anti-reflection coatings provide <0.25% reflection at the coating's design wavelengths.

Technical Information



Compatible Mounts