

TECHSPEC[®] 15mm, Uncoated, High Tolerance N-BK7 Right Angle Prism



N-BK7 High Tolerance Right Angle Prisms

Stock #32-545 20+ In Stock

-

1

+

₹7,965

ADD TO CART

Volume Pricing	
Qty 1-5	₹7,965 each
Qty 6-25	₹6,345 each
Qty 26-49	₹5,985 each
Need More?	Request Quote

Product Downloads


General	
Right Angle Prism	Type:
Physical & Mechanical Properties	
+0/-0.1	Dimensional Tolerance (mm):
Protective as needed	Bevel:

21.20	Length of Hypotenuse (mm):
15.00	Length of Legs (mm):
Optical Properties	
±15	Angle Tolerance (arcsec):
Uncoated	Coating:
N-BK7	Substrate: ☐
40-20	Surface Quality:
Left-Handed	Image Orientation:
90	Ray Deviation (°):
350 - 2200	Wavelength Range (nm):
1.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ray Deviation of 90°
 - Left Handed Image
 - Low Arcsecond Angle Tolerance
 - Additional [Right Angle Prism](#) Options Available
- TECHSPEC® High Tolerance N-BK7 Right Angle Prisms are generally used to bend image paths or redirect light at 90°. This process produces a left-handed image, depending on the prism's orientation, the image may be inverted or reverted. Right angle prisms can also be combined for image/beam displacement. TECHSPEC® High Tolerance N-BK7 Right Angle Prisms feature low arcsecond angle tolerance and are made from precision N-BK7 for use in a variety of visible light applications. These prisms are available uncoated, with a protective aluminum overcoat, or VIS° & aluminized.

Technical Information





Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram