

165mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-181 CLEARANCE CONTACT US

⊖ 1 ⊕ ₹52,805

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | ₹52,805 each |
| Need More? | Request Quote |

Product Downloads

SPECIFICATIONS

General

F-Theta Lens Type:

Physical & Mechanical Properties

109 Maximum Diameter (mm):

| | |
|---------------------------------|---|
| 219.1 | Flange Distance (mm): |
| 12 | Input Beam Diameter, 1/e² (mm): |
| 54.0 | Maximum Length (mm): |
| Optical Properties | |
| 1064 | Design Wavelength DWL (nm): |
| 165.10 | Focal Length FL (mm): |
| ±28.50 | Scan Angle (°): |
| 116.2 x 116.2 | Scan Field (mm): |
| Not Specified | Telecentricity (°): |
| ≥95 | Transmission (%): |
| 188.1 | Working Distance (mm): |
| 1064 | Wavelength Range (nm): |
| 26 | Focus Size Diameter, 1/e² (μm): |
| Threading & Mounting | |
| M85 x 1.0 | Mounting Threads: |
| Regulatory Compliance | |
| View | Certificate of Conformance: |

PRODUCT DETAILS

- Ideal for Laser Scanning Applications
- Diffraction Limited Across the Scan Field with Low Wavefront Error
- Long Working Distances and Large Scan Areas
- [Galvanometers](#), [Beam Expanders](#), and [Laser Sources](#) Also Available

Edmund Optics® F-Theta Lenses are designed to provide flat fields at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta Lenses feature compact form factors, offer a wide range of focal lengths up to 273mm, and large scan fields up to 164mm (X) x 164mm (Y). Optimized for common fiber laser sources and Nd:YAG fundamental or second harmonic, these lenses are available in design wavelengths of 532nm and 1064nm with common mounting threads for easy integration into galvo systems. Edmund Optics® F-Theta Lenses are a cost-effective solution for laser scanning and laser processing applications including laser marking, engraving, cutting, drilling, and 3D modeling.