

16mm Dia. x 10.8mm FL, Uncoated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#34-459** **20+ In Stock**

☐ [Other Coating Options](#)

-

1

+

₹2,491

ADD TO CART

Volume Pricing	
Qty 1-10	₹2,491 each
Qty 11-49	₹2,219 each
Need More?	Request Quote

Product Downloads

General	
Condenser Lens	Type:
Note: Click here for more information on the ISO 10110 surface quality specification.	
Physical & Mechanical Properties	
16.00 +/-0.3	Diameter (mm):

≤25	Centering (arcmin):
12.80	Clear Aperture CA (mm):
2.6	Edge Thickness ET (mm):
8.00 ±0.20	Center Thickness CT (mm):
Protective as needed	Bevel:
16.0	Diameter of Asphere (mm):
Plano	Shape of Back Surface:

Optical Properties	
10.80 @ 587.6nm	Effective Focal Length EFL (mm):
0.74	Numerical Aperture NA:
5.90	Back Focal Length BFL (mm):
N-F2	Substrate: □
±5	Focal Length Tolerance (%):
Uncoated	Coating:
Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2	Surface Quality:
0.68	f/#:
Plano	Radius R ₂ (mm):
350 - 2000	Wavelength Range (nm):
Infinite	Conjugate Distance:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:
Poland	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Hardened for Improved Durability
- High Numerical Apertures
- Ideal for Illumination Applications

Molded Aspheric Condenser Lenses are pressed, hardened, and annealed to meet precise optical and mechanical specifications. The hardening process improves the durability of the lenses, making them less susceptible to thermal shock and scratching than traditionally polished lenses. These Molded Aspheric Condenser Lenses are ground and polished on the second surface, enhancing the overall precision of the lenses. Molded Aspheric Condenser lenses are ideal for a wide range of illumination and detection applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

Technical Information



;