

TECHSPEC® 16mm, f/1.8 UCi Series Fixed Focal Length Lens



16mm UCi Series Fixed Focal Length Lens



Stock #33-883 **1 In Stock**

MRP ₹23,440

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹23,440 each
Need More?	Request Quote

Product Downloads

General

UCi Series **Product Family:**

Fixed Focal Length Lens **Type:**

No **IR Cut Filter:**

Imaging Lens Type:

Physical & Mechanical Properties

Fixed Iris Option:

26.70

Length (mm):

18

Maximum Diameter (mm):

25

Outer Diameter (mm):

13

Weight (g):

0

Maximum Rear Protrusion (mm):

25.5

Maximum Length (mm):

Optical Properties

Horizontal Field of View @ Max Sensor Format:

98.5mm - 25.3°

Field of View at Max Sensor Format:

Horizontal: 93.6mm - 25.3°

Vertical: 70.2mm - 19.1°

Diagonal: 117mm - 31.3°

Horizontal Field of View, 1/1.8" Sensor:

93.6mm - 25.3°

Horizontal Field of View, 1/2" Sensor:

83.2mm - 22.5°

Horizontal Field of View, 1/2.5" Sensor:

75.4mm - 20.5°

Horizontal Field of View, 1/3" Sensor:

62.4mm - 17.0°

Horizontal Field of View, 1/4" Sensor:

46.8mm - 12.8°

Maximum Image Circle (mm):

9.00

Numerical Aperture NA, Object Side:

0.0207

Number of Elements (Groups):

7 (5)

Focal Length FL (mm):

16.00

Working Distance (mm):

200 - ∞

Aperture (f/#):

f/1.8

Coating:

N4 MgF₂

Coating Specification:

N4 MgF₂

Entrance Pupil Position (mm):

10.68

Object Space Principal Plane (mm):

20.18

Image Space Principal Plane (mm):

-6.67

Maximum Distortion (%):

-0.53

Exit Pupil Position (mm):

-29.94

Lens Wavelength Range:

VS

Sensor

Optimized Sensor Format:

1/2.5"

Maximum Sensor Format:

1/1.8"

Pixel Size (μm):

1.85

Threading & Mounting

Filter Thread:
M18 x 0.50 (Male)

Mount:
S-Mount (M12 x 0.5)

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels $\leq 2.2\mu\text{m}$ and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

Note: For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


Technical Information




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Distortion Plot




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f1.8



#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f1.8



#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f1.8



#33-883, 16mm, f/1.8 UCi Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f1.8

Compatible Cameras