

TECHSPEC[®] 15mm Protected Gold Coated, UV Fused Silica Right Angle Mirror



Stock #22-560 12 In Stock

-

1

+

₹20,241

ADD TO CART

Volume Pricing	
Qty 1-5	₹20,241 each
Qty 6-25	₹16,193 each
Qty 26-49	₹15,181 each
Need More?	Request Quote

Product Downloads

General

Right Angle MirrorType:

Physical & Mechanical Properties

15.00Length of Legs (mm):

+0.00/-0.10Dimensional Tolerance (mm):

Protective as needed	Bevel:
19.08 x 13.50	Clear Aperture CA (mm):
21.20	Length of Hypotenuse (mm):
Optical Properties	
λ/20	Surface Flatness (P-V):
Fused Silica (Corning 7980)	Substrate: □
20-10	Surface Quality:
Ravg >96% @ 700 - 2000nm Ravg >96% @2000 - 10,000nm	Coating Specification:
Protected Gold (700-10000nm)	Coating:
Metal	Coating Type:
0.70 - 10	Wavelength Range (μm):
700 - 10000	Wavelength Range (nm):
±15	Angle Tolerance (arcsec):
0.8 J/cm ² @ 1064nm, 10ns	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Precision Fused Silica Substrates for Increased Thermal Stability
 - Ideal for System Alignment
 - Enhanced Aluminum, Protected Gold, and Protected Silver Coatings Available
- TECHSPEC® λ/20 Fused Silica Right Angle Prism Mirrors feature broadband metal coatings and a ±15 arcsecond angular tolerance for applications that require precision alignment. These highly reflective right angle mirrors simplify alignment when mounting and are easily integrated into systems that redirect light at 90°. TECHSPEC® λ/20 Fused Silica Right Angle Prism Mirrors utilize Fused Silica substrates for high temperature environments and their precision design and tolerances enable easy system integration. Coating options feature >95% reflectivity from 450nm to the long wave infrared (IR).

Technical Information





Image above shows light reflecting off the coated hypotenuse.



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
