

[See all 5 Products in Family](#)

TECHSPEC® 16mm Focal Length, UAV Series Fixed Focal Length Lens



TECHSPEC® UAV Series Fixed Focal Length Lenses



Stock #22-836 **4 In Stock**

MRP ₹89,208

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹89,208 each
Need More?	Request Quote

Product Downloads

General

UAV Series **Product Family:**

Fixed Focal Length Lens **Type:**

Infinite Conjugate **Imaging Lens Type:**

Physical & Mechanical Properties

Variable **Iris Option:**

92.23	Length (mm):
50.0	Maximum Diameter (mm):
50	Outer Diameter (mm):
223	Weight (g):
4.0	Maximum Rear Protrusion (mm):
88.77	Maximum Length (mm):
88.23	Minimum Length (mm):

Optical Properties

49.5°	Horizontal Field of View @ Max Sensor Format:
49.5°	Horizontal Field of View, 1.2" Sensor:
58.2°	Horizontal Field of View, 1.1" Sensor:
53.6°	Horizontal Field of View, 1" Sensor:
38.2°	Horizontal Field of View, 2/3" Sensor:
31.5°	Horizontal Field of View, 1/1.8" Sensor:
19.30	Maximum Image Circle (mm):
0.00057	Numerical Aperture NA, Object Side:
9 (8)	Number of Elements (Groups):
425 - 675	Wavelength Range (nm):
16.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
FOV @ Max Sensor Format, H x V (mm): Horizontal: 49.5° Vertical: 43.3° Diagonal: 62.8°	
f/2.8 - f/16	Aperture (f/#):
425 - 675 BBAR	Coating:
425 - 675 BBAR	Coating Specification:
26.984	Entrance Pupil Position (mm):
-34.86	Object Space Principal Plane (mm):
-15.78	Image Space Principal Plane (mm):
1.5	Maximum Distortion (%):
-31.232	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

1.2"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M49.0 X 0.50 (Female)	Filter Thread:
M49.0 X 0.50	Front Thread:
C-Mount	Mount:

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 235:

Compliant

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000


Product Details

- Compact, Infinite Conjugate Lens Ideal for Photogrammetry
- 8mm, 12mm, 16mm, 25mm, and 35mm Focal Lengths
- 1.2", C-Mount Lens
- Up to 24.4 MegaPixels, 2.7µm Pixel Size Sensors


TECHSPEC® UAV Series Fixed Focal Length Lenses are compact, lightweight infinite conjugate lenses designed for the 4th Generation Sony Pregius 1.2" IMX530 and IMX540 sensors for mounting on autonomous vehicles and drones. These lenses are designed with a low Ground Separation Distance (GSD) to enable accurate survey results, and are available in 8mm, 12mm, 16mm, 25mm, and 35mm focal length options. The f/2.8 aperture provide increased light throughput and high-resolution performance. TECHSPEC® UAV Series Fixed Focal Length Lenses are C-Mount and feature a locking focus and iris rings to prevent unwanted adjustments, as well as a front filter thread for integrating standard [optical filters](#). These lenses are ideal for Drone Mapping and Surveying, Aerial Imaging, and Photogrammetry applications.

Note: Call for OEM Quantity and Pricing


Technical Information




#22-836 - 16mm Focal Length, UAV Series Fixed Focal Length Lens, Distortion Plot



#22-836 - 16mm Focal Length, UAV Series Fixed Focal Length Lens, Relative Illumination Plot



#22-836 - 16mm Focal Length, UAV Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, Infinity Working Distance, f2.8



#22-836 - 16mm Focal Length, UAV Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, Infinity Working Distance, f4