

[See all 5 Products in Family](#)

**TECHSPEC® 15mm VIS, 50R/50T, Non-Polarizing In-Line Cube Beamsplitter**



Stock #20-095 **16 In Stock**

MRP ₹33,294

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹33,294 each
Qty 6-25	₹28,249 each
Qty 26-99	₹24,517 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

**Note:**  
Absorptive Surface Treatment on Blackened Face

**Type:**  
Non-Polarizing Beamsplitter

**Physical & Mechanical Properties**

**Bevel:**  
Protective as needed

>90	<b>Clear Aperture (%)</b> :
Cube	<b>Construction</b> :
15.0 x 15.0 x 15.0	<b>Dimensions (mm)</b> :
<b>Optical Properties</b>	
≤2	<b>Beam Deviation (arcmin)</b> :
VS	<b>Coating</b> :
R <sub>avg</sub> <0.5% @ 430 - 670nm	<b>Coating Specification</b> :
50/50	<b>Reflection/Transmission Ratio (R/T)</b> :
N-BK7	<b>Substrate</b> : <input type="checkbox"/>
40-20	<b>Surface Quality</b> :
430 - 670	<b>Wavelength Range (nm)</b> :
<6%	<b> Ts-Tp </b> :
45 ±10	<b>Absolute Transmission (%)</b> :
45 ±5	<b>Average Transmission (%)</b> :
1.25	<b>Power (fringes) @ 632.8nm</b> :
0.25	<b>Irregularity (fringes) @ 632.8nm</b> :

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance</b> :
Singapore	<b>Country of Origin</b> :
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By</b> :

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Significantly Reduces Glare and Interference
- 50/50 Reflection/Transmission Ratio
- Ideal for In-Line Illumination

TECHSPEC® Non-Polarizing In-Line Cube Beamsplitters are specialized versions of [TECHSPEC® Broadband Non-Polarizing Cube Beamsplitters](#) that include a proprietary surface treatment on one surface. This feature reduces glare, interference artifacts, and improves image contrast. These cube beamsplitters are ideal for in-line illumination applications and are particularly useful in a wide range of applications that are sensitive to ghost reflections. TECHSPEC® Non-Polarizing In-Line Cube Beamsplitters are constructed from high tolerance right angle prisms and are Broadband Anti-Reflection (BBAR) coated to maximize transmission at specified wavelengths. These beamsplitters are spectrally flat within their design wavelength range, reducing undesirable effects caused by changes in the angle of incidence or converging/diverging beams.