

TECHSPEC® 18.0mm Dia. x 18.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#48-424** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹3,176.00**

ADD TO CART

Qty 1-9
₹3,176.00
Qty 10+
₹2,849.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):
18.00 @ 587.6nm

Back Focal Length BFL (mm): 15.20
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Edge Thickness ET (mm): 1.76
Radius R₁ (mm): 14.13
Clear Aperture CA (mm): 17
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View